



注) NOTE.

- △ フリクションロック構成:  
 FRICTION LOCK CONFIGURATION:  
 4極までは1箇所  
 4CKT AND UNDER - 1LOCK  
 5極以上は2箇所  
 5CKT AND OVER - 2LOCKS
- 2. 嵌合相手: 5102-N  
 MATES WITH HOUSING: 5102-N
- △ スリット構成:  
 SLIT CONFIGURATION:  
 4極以下はなし  
 4CKT AND UNDER - NO SLIT  
 5及び6極は1箇所  
 5 AND 6CKTS - 1 SLIT  
 7極以上は2箇所  
 7CKT AND OVER - 2 SLITS

29-11-0153	5240-151	35	38.7	4.1	5	38.3		15
▲ -0143	▲ -141	32.5	36.2	38.6	5	35.8		14
	-0133	-131	30	33.7	5	33.3		13
	-0123	-121	27.5	31.2	5	30.8		12
	-0113	-111	25	28.7	5	28.3		11
	-0103	-101	22.5	26.2	5	25.8		10
	-0093	-091	20	23.7	5	23.3		9
	-0083	-081	17.5	21.2	5	20.8		8
	-0073	-071	15	18.7	5	18.3		7
	-0063	-061	12.5	16.2	5	15.8		6
	-0053	-051	10	13.7	3.75	13.3		5
	-0043	-041	7.5	11.2	7.5	10.8		4
▼ -0033	▼ -031	5	8.7	11.1	5	8.3		3
29-11-0023	5240-021	2.5	6.2	8.6	2.5	5.8		2
EDP. NO.	ENG. NO.	B	C	(A)	(E)	(D)		極数 CKT.

DO NOT SCALE DRAWING

EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	EC NO. DRWN: CHK: APPR:	REDRAWN EC NO. JC2000-0629 DRWN: K.KOHAMA 000/3/28 CHK: T.YAMAGUCHI 007/3/30 APPR: M.FUKUSHIMA 007/3/30	MATERIAL 材料	GENERAL TOLERANCES: (UNLESS SPECIFIED) 一般公差	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION	DIMENSIONS: <input type="checkbox"/> mm <input type="checkbox"/> INCH <input checked="" type="checkbox"/> mm ONLY	SHT	REV
					NYLON66, 94V-0 色: オフホワイト COLOR: OFF WHITE	10 UNDER 未満	±0.2	DRAWN BY & DATE K.KOHAMA 007/3/28	TITLE: MINI. SPOX PLUG HSG.	REVISE ON CAD ONLY		
					FINISH 仕上り	10 OVER 以上	30 UNDER 未満	±0.25	CHECKED BY & DATE T.YAMAGUCHI 007/3/30	MATERIAL NO. 5240-***1	DRAWING NO. SD-5240-NI	SHEET NO. 1
					WIRE RANGE 適用線径範囲	30 OVER 以上	±0.3	APPROVED BY & DATE M.FUKUSHIMA 007/3/30	CAD FILENAME S5240.S01	SIZE B		
INS. RANGE 被覆外径	ANGLE 角度	±3°	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.				EN-02J(097) MXJ-54					