

# PS3-2-0

ABB contact for United  
States of America



## General Information

---

<b>Extended Product Type:</b>	PS3-2-0
<b>Product ID:</b>	1SAM101937R0012
<b>EAN:</b>	4013614313820
<b>Catalog Description:</b>	PS3-2-0 3-Phase Busbar
<b>Long Description:</b>	PS3-2-0 Busbar for 2 devices

---

## Categories

---

Products » Low Voltage Products and Systems » Control Products » Manual Motor Starters » Manual Motor Starters Accessories

---

## Ordering

---

<b>EAN:</b>	4013614313820
<b>Minimum Order Quantity:</b>	1 piece
<b>Customs Tariff Number:</b>	85389099

---

## Container Information

---

<b>Package Level 1 Width:</b>	46.0 mm
<b>Package Level 1 Length:</b>	120.0 mm
<b>Package Level 1 Height:</b>	80.0 mm
<b>Package Level 1 Gross Weight:</b>	0.410 kg
<b>Package Level 1 EAN:</b>	4013614487910
<b>Package Level 1 Units:</b>	10 piece

---

## Dimensions

---

<b>Product Net Width:</b>	98.5 mm
<b>Product Net Height:</b>	31.5 mm
<b>Product Net Depth:</b>	13.0 mm
<b>Product Net Weight:</b>	0.038 kg

---

## Technical

---

<b>Rated Operational Voltage:</b>	690 V
<b>Rated Operational Current (I<sub>o</sub>):</b>	63 A
<b>Standards:</b>	IEC/EN 60947-1 IEC/EN 60947-4-1 UL 60947-1 UL 60947-4-1
<b>Product Name:</b>	3-Phase Busbar
<b>Suitable For:</b>	MS325 MO325
<b>Suitable for Product Class:</b>	Manual Motor Starters

---

## Environmental

---

<b>Ambient Air Temperature:</b>	Operation -20 ... +50 °C Storage -20 ... +70 °C
<b>RoHS Status:</b>	Following EU Directive 2002/95/EC August 18, 2005 and amendment

---

## Technical UL/CSA

**Maximum Operating Voltage UL/CSA:** Main Circuit 600 V  
**Ampere Rating UL/CSA:** 63 A

## Certificates and Declarations (Document Number)

**cUL Certificate:** 1SAA963001-1701  
**Declaration of Conformity - CE:** 1SAD938509-0056  
**GOST Certificate:** 1SAA918000-2703  
**RoHS Information:** 1SAA918001-4402  
**UL Certificate:** 1SAA963001-1602

## Classifications

**eClass:** 7.0 27379201  
**E-nummer:** 3111430  
**Object Classification Code:** W  
**UNSPSC:** 39121100

