



Part Number : [638280100](#)

Product Description : Hand Crimp Tool for Standard .093" Pin and Socket Crimp Terminals, Claspcon Pin and Socket Crimp Terminals, and Commoning Connector Crimp Terminals, 18 AWG

Series Number : 207129

Status : Active

Product Category : Crimp Presses and Crimp Hand Tools



Documents & Resources

Tooling Specifications

[ATS-638280100-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	Not Relevant
EU ELV	Not Relevant
Low-Halogen Status	Not Relevant
REACH SVHC	Not Reviewed per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Not Reviewed per EU 2015/863

Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

Substances of Interest

- PFAS

EU RoHS Certificate of Compliance

Additional Product Compliance Information

Part Details

General

Status	Active
Category	Crimp Presses and Crimp Hand Tools
Series	207129
Description	Hand Crimp Tool for Standard .093" Pin and Socket Crimp Terminals, Claspcn Pin and Socket Crimp Terminals, and Commoning Connector Crimp Terminals, 18 AWG
Comments	See Tooling Specification (PDF) Above
Function	Crimp
Geographic Area	Global
Level of Automation	Manual
More Detailed Tech Information	toolingsupport@molex.com
Product Name	Claspcn,Commoning Connector,Standard .093"
Tool Type	Hand Crimp Tool
UPC	191128795982
Warranty Disclaimer	CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector

	<p>system is that of the customer.</p> <p>Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.</p>
--	--

Applicable Parts

Description	Part Number
Claspcn Crimp Terminal Socket, Tin (Sn) Plated Brass Contact, 24-16 AWG, Bag	<u>02081102</u>
Claspcn Crimp Terminal Socket, Tin (Sn) Plated Brass Contact, 24-16 AWG, Reel	<u>02081101</u>
Claspcn Crimp Terminal Socket, Tin (Sn) Plated Brass Contact, 24-16 AWG, Reel	<u>02085101</u>
2.36mm Diameter, Standard .093" Pin and Socket Crimp Grounding Terminal, Series 1973, Male, with Tin (Sn) Plated Brass Contact, 22-18 AWG, Reel	<u>02098103</u>