

© - TE Connectivity. All Rights Reserved.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	1	NEW DRAWING	05SEP2024	LP	MY

XXXXXX

SERIES

LHE LED HOLDER BLOCK

XX

COLOR:

RD	RED
GR	GREEN
YL	YELLOW
BL	BLUE
BK	BLACK
WH	WHITE
OR	ORANGE

XXXX

VOLTAGE:

12	12V AC/DC
24	24V AC/DC
240	240VAC

TEST PARAMETERS	SPECIFICATION
Product	LED Holder
Rated Voltage	12V AC/DC, 24V AC/DC, 240 AC
Operating Voltage	-20% to +10% of rated voltage
Type of LED	Side View SMD LED's
Available Colours	Red / Green / Yellow / Amber / Blue / White
Life / Warranty	0.1 Million burning hours / 24 months**
Operating Frequency	50 / 60 Hz
Operating Temperature	-25°C to 65°C
Storage Temperature	-30°C to 70°C
Wire Termination Capacity	0.5mm ² , 1.5 – 2.5 mm ²
Terminal Torque	0.8 Nm
LPGP	Available
Surge Test	2KV
HV Test for 60 sec.	1.5KV
Degree of Protection	Above Panel : IP65 For Terminals : IP20

7.3

45.5

9.3

24

21

23.9

32.4

22

9.7

LED HOLDER ORANGE 12VAC/DC	ORANGE	12VAC/DC	LHEOR12	1-2492721-8
LED HOLDER WHITE 12VAC/DC	WHITE	12VAC/DC	LHEWH12	1-2492721-7
LED HOLDER BLUE 12VAC/DC	BLUE	12VAC/DC	LHEBL12	1-2492721-6
LED HOLDER YELLOW 12VAC/DC	YELLOW	12VAC/DC	LHEYL12	1-2492721-5
LED HOLDER GREEN 12VAC/DC	GREEN	12VAC/DC	LHEGR12	1-2492721-4
LED HOLDER RED 12VAC/DC	RED	12VAC/DC	LHERD12	1-2492721-3
LED HOLDER ORANGE 24VAC/DC	ORANGE	24VAC/DC	LHEOR24	1-2492721-2
LED HOLDER WHITE 24VAC/DC	WHITE	24VAC/DC	LHEWH24	1-2492721-1
LED HOLDER BLUE 24VAC/DC	BLUE	24VAC/DC	LHEBL24	1-2492721-0
LED HOLDER YELLOW 24VAC/DC	YELLOW	24VAC/DC	LHEYL24	2492721-9
LED HOLDER GREEN 24VAC/DC	GREEN	24VAC/DC	LHEGR24	2492721-8
LED HOLDER RED 24VAC/DC	RED	24VAC/DC	LHERD24	2492721-7
LED HOLDER ORANGE 240VAC	ORANGE	240VAC	LHEOR240	2492721-6
LED HOLDER WHITE 240VAC	WHITE	240VAC	LHEWH240	2492721-5
LED HOLDER BLUE 240VAC	BLUE	240VAC	LHEBL240	2492721-4
LED HOLDER YELLOW 240VAC	YELLOW	240VAC	LHEYL240	2492721-3
LED HOLDER GREEN 240VAC	GREEN	240VAC	LHEGR240	2492721-2
LED HOLDER RED 240VAC	RED	240VAC	LHERD240	2492721-1
DESCRIPTION	LED COLOR	LED VOLTAGE	TE SMART PN	TE PN

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± 0.5
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	-

MATERIAL

-

DWN
LINGANATHAN P
CHK
MANOJ YADAV
APVD
MANOJ YADAV

05SEP2024
05SEP2024
05SEP2024

PRODUCT SPEC
APPLICATION SPEC
WEIGHT

—
—
—

05SEP2024
NAME
LED HOLDER

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-2492721

RESTRICTED TO
—

CUSTOMER DRAWING

SCALE
1:1

SHEET
1 OF 1

REV
1

1470-19 (1/15)