




PRODUCT-DETAILS

JSHD2C type E

JSHD2C type E Three-position single pushbutton



General Information	
Extended Product Type	JSHD2C type E
Product ID	2TLA020001R1000
EAN	7350024456837
Catalog Description	JSHD2C type E Three-position single pushbutton
Long Description	The JSHD2C Type E is a three-position pushbutton with gold plated contacts and 3 leads, each 190 mm. The force needed to actuate the push-button from middle to bottom is 20 N. Three-position pushbuttons are usually used in pair in a three-position device.

Ordering	
Minimum Order Quantity	1 piece
Customs Tariff Number	85369095
Product Main Type	JSHD2
Product Name	Three-position single pushbutton
Function	Three-position single pushbutton
Status Indicator	No

Popular Downloads

Data Sheet, Technical Information	2TLC010097L0201
CAD Dimensional Drawing	2CDC001079B0201
Marketing Video	2TLC010018N0201

Installation

Instructions and Manuals	2TLC010097L0201
--------------------------	-----------------

Dimensions

Product Net Depth / Length	13.5 mm
Product Net Height	29.25 mm
Product Net Width	26.55 mm
Product Net Weight	0.01 kg
CAD Dimensional Drawing	2CDC001079B0201

Safety Information

Certification Agency	CE cURus Kiwa
B10d Value	Operations to Bottom Position 968 000 Operations to Middle Position 2 million

Technical

Communication Interface	Contacts
Connection Configuration	3 leads, 190 mm each
Number of Contacts NC	1
Number of Contacts NO	1
Rated Operational Current DC-12 (I _e)	(24 V) 0.02 A
Technical Information	Foff: 20 N; Mechanical service life: > 1 million cycles, top to middle position, > 100 000 cycles, middle to bottom position

Environmental

Ambient Air Temperature	Operation -10 ... 55 °C Storage -40 ... +85 °C
Degree of Protection	IP54
Material	Contact: Au Housing: POM 20% GF (yellow) Plunger: PBT (Black)

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2022-006480
RoHS Declaration	2CMT2022-006499
RoHS Information	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006522
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Certificates and Declarations

CQC Certificate	No certification needed
cULus Certificate	2TLC010153D0201
cURus Certificate	2TLC010153D0201
Declaration of Conformity - CCC	No declaration needed
Declaration of Conformity - CE	2TLC172022D0201
Declaration of Conformity - UKCA	2TLC010152D0201
SEMKO Certificate	2TLC172032D0201

Container Information

Package Level 1 Units	bag 1 piece
Package Level 1 Width	100 mm
Package Level 1 Depth / Length	170 mm
Package Level 1 Height	14 mm
Package Level 1 Gross Weight	0.01 kg
Package Level 1 EAN	7350024456837

External Classifications and Standards

eClass	V11.0 : 27371238
ETIM 7	EC002571 - Agreement switch
ETIM 8	EC002571 - Agreement switch
ETIM 9	EC002571 - Agreement switch
IDEA Granular Category Code (IGCC)	5210 >> Push button switch
UNSPSC	39122216
Object Classification Code	B

Categories

Low Voltage Products and Systems → Control Products → Safety Products → Safety Control Devices → JSHD

