



ALPHA 630, Floor-mounted cabinet, IP44, Protection class 2, H: 1950 mm, W: 1050 mm, T: 210 mm, RAL 7035

| Model                                              |     |                       |       |
|----------------------------------------------------|-----|-----------------------|-------|
| product brand name                                 |     | ALPHA                 |       |
| product designation                                |     | Free-standing cabinet |       |
| surface processing                                 |     | powder-coated         |       |
| Protection class                                   |     |                       |       |
| protection class IP                                |     | IP44                  |       |
| operating resource protection class                |     | Safety class 2        |       |
| IK protection class                                |     | IK09                  |       |
| suitability for interaction lightning protection   |     | Yes                   |       |
| suitability for use for outside use                |     | No                    |       |
| Appearance                                         |     |                       |       |
| RAL color number                                   |     | 7035                  |       |
| product component                                  |     |                       |       |
| • cable entry                                      | Yes |                       |       |
| • mounting plate                                   | No  |                       |       |
| product extension optional side-by-side mounting   |     | Yes                   |       |
| number of rows                                     |     | 48                    |       |
| Mechanical Design                                  |     |                       |       |
| height                                             |     | 1 950 mm              |       |
| width                                              |     | 1 050 mm              |       |
| depth                                              |     | 210 mm                |       |
| installation depth                                 |     | 210 mm                |       |
| number of modular width units                      |     | 576                   |       |
| number of modular width units per DIN mounting bar |     | 12                    |       |
| fastening method                                   |     | floor mounting        |       |
| net weight                                         |     | 63 kg                 |       |
| material of the enclosure                          |     | Steel                 |       |
| Approvals Certificates                             |     |                       |       |
| General Product Approval                           |     | Test Certificates     | other |



[Special Test Certificate](#)

[Miscellaneous](#)

[Confirmation](#)

Environment

[Environmental Conformations](#)

[Environmental Conformations](#)

#### Further information

##### Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

##### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

##### Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8GK1332-8KA42>

##### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8GK1332-8KA42>

##### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mlfb=8GK1332-8KA42](http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GK1332-8KA42)

##### CAX-Online-Generator

<http://www.siemens.com/cax>

##### Tender specifications

<http://www.siemens.com/specifications>



last modified:

5/26/2025 

