


Nickel-Plated Brass Adaptors

0934 Tailpiece Adaptor for Polymer Tubing, Male BSPT Thread


Nickel-plated brass



ØD	C		F	L	L1	Kg
6	R1/8	0934 06 10	12	31.5	19	0.009
	R1/4	0934 06 13	14	35	19	0.014
7	R1/8	0934 07 10	12	31.5	19	0.009
	R1/4	0934 07 13	14	35	19	0.014
8	R1/8	0934 08 10	12	31.5	19	0.010
	R1/4	0934 08 13	14	35	19	0.015
9	R1/4	0934 09 13	14	35	19	0.015
	R3/8	0934 09 17	17	35.5	19	0.021
10	R1/2	0934 09 21	22	38.5	19	0.032
	R1/8	0934 10 10	12	32.5	20	0.011
	R1/4	0934 10 13	14	36	20	0.016
	R3/8	0934 10 17	17	36.5	20	0.021
12	R1/2	0934 10 21	22	39.5	20	0.033
	R1/4	0934 12 13	14	36	20	0.016
14	R3/8	0934 12 17	17	36.5	20	0.021
	R1/2	0934 12 21	22	39.5	20	0.033
16	R3/8	0934 14 17	17	38.5	22	0.025
	R1/2	0934 14 21	22	41.5	22	0.036
18	R3/8	0934 16 17	17	38.5	22	0.026
	R1/2	0934 16 21	22	41.5	22	0.037
20	R3/4	0934 16 27	27	45	22	0.055
	R1/2	0934 17 21	22	43.5	24	0.041
17	R3/8	0934 18 17	19	40.5	24	0.035
	R1/2	0934 18 21	22	43.5	24	0.044
18	R3/4	0934 18 27	27	47	24	0.064
	R1/2	0934 20 21	22	43.5	24	0.041

0902 Equal and Unequal Adaptor, Female BSPP and Metric Thread


Nickel-plated brass



C1	C2		F	L	Kg
M5x0.8	M5x0.8	0902 00 19	8	11	0.003
	G1/8	0902 19 10	14	13.5	0.009
G1/8	G1/8	0902 00 10	14	15	0.010
	G1/4	0902 10 13	17	19	0.017
G1/8	G3/8	0902 10 17	22	20	0.028
	G1/4	0902 00 13	17	22	0.019
G1/4	G3/8	0902 13 17	22	22.5	0.031
	G1/2	0902 13 21	26	24	0.033
G3/8	G3/8	0902 00 17	22	23	0.035
	G1/2	0902 17 21	24	26	0.036
G1/2	G1/2	0902 00 21	26	28	0.049
	G3/4	0902 21 27	32	30	0.078
G3/4	G3/4	0902 00 27	32	32	0.076

0935 Tailpiece Adaptor for Polymer Tubing, Male BSPP Thread

Nickel-plated brass



ØD	C		E	F	L	L1	Kg
6	G1/8	0935 06 10	8	12	28.5	19	0.007
8	G1/4	0935 08 13	11	15	31.5	19	0.012
12	G1/2	0935 12 21	14.5	24	36	20	0.033

0950MB Maintenance Kit, BSPP Thread

Nickel-plated brass



	H	L	L1	Kg
0950 00 00 02	81	413	330	3.500

A selection of 250 references covering the most-used products
Other packaging available: Ref 0950 00 00 02x6 per 6 units

0950M0 Maintenance Kit, BSPT Thread

Nickel-plated brass



	H	L	L1	Kg
0950 00 00 03	81	413	330	3.500

A selection of 216 references covering the most-used products
Other packaging available: Ref 0950 00 00 03x6 per 6 units