



**Part Number :** [1731120419](#)


**Product Description :** FCT DIN Coaxial Contact, Female, Straight, Crimp, 50 Ohms, 1.30µm Gold Plating, for RG-58CU or RG-141AU Cable

**Series Number :** 173112

**Status :** Active

**Product Category :** D-Sub Contacts

**Engineering Number :** FDS005S102



---

## Documents & Resources

### Drawings

[1731120419 sd.pdf](#)

### Specifications

[2195600660-000.pdf](#)

[1731120009-PK-000.pdf](#)

[2195600660-000.pdf](#)

---

## Product Environment Compliance

### Compliance

GADSL/IMDS	Not Relevant
China RoHS	per SJ/T 11365-2006
EU ELV	Not Relevant
Low-Halogen Status	Not Reviewed per IEC 61249-2-21
REACH SVHC	Contains Lead; pyrochlore, antimony lead yellow per D(2024)7663-DC (21 Jan 2025)
EU RoHS	Compliant with Exemption 6(c) per EU 2015/863

### Compliance Statements

- EU RoHS
- REACH SVHC
- Low-Halogen

## Industry Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

## Substances of Interest

- PFAS

## EU RoHS Certificate of Compliance

## Additional Product Compliance Information

---

## Part Details

### General

Status	Active
Category	D-Sub Contacts
Series	173112
Description	FCT DIN Coaxial Contact, Female, Straight, Crimp, 50 Ohms, 1.30µm Gold Plating, for RG-58CU or RG-141AU Cable
Contact Type	Coaxial
Magnetic	Yes
Product Name	FCT Products
Type	Mixed Layout
UPC	191128195812

### Electrical

Current - Maximum per Contact	2.0A
Impedance	50Ω

### Physical

Durability (mating cycles min)	500
Gender	Female
Material - Contact	Copper Alloy
Material - Plating Mating	Gold over Nickel
Material - Plating Termination	Gold over Nickel
Net Weight	1.500/g

Orientation	Straight
Packaging Type	Bag
Plating min - Mating	1.300µm
Plating min - Termination	0.200µm
Temperature Range - Operating	-55° to +135°C
Termination Style	Crimp
Wire/Cable Type	RG-141AU, RG-58CU

## Mates With / Use With

### Use with Part(s)

Description	Part Number
Use With	FCT Mixed Layout Connectors

---

## Application Tooling

### Global

Description	Part Number
FCT Removal Tool for Size 8 Contacts	<u>1731121747</u>