

OCS PANEL 1210 PC - Mounting panel



1471786

<https://www.phoenixcontact.com/gb/products/1471786>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Mounting panel for housing size of 12" x 10", material: polycarbonate, color: white



Your advantages

- Internationally certified housing system
- Special plastic enables safe continuous operation
- Provides protection against the ingress of jet water
- Withstands even heavy mechanical strain

Commercial data

Item number	1471786
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	ACFDBZ
Product key	ACFDBZ
GTIN	4063151875589
Weight per piece (including packing)	287 g
Weight per piece (excluding packing)	0.292 g
Customs tariff number	39269097
Country of origin	DE

OCS PANEL 1210 PC - Mounting panel



1471786

<https://www.phoenixcontact.com/gb/products/1471786>

Technical data

Product properties

Product type	Mounting plate
Housing type	Outdoor housing
Housing series	OCS
Product family	OCS..1210..

Dimensions

Width	222 mm
Height	272 mm
Depth	4 mm

Material specifications

Color	white (RAL 9010)
Material ()	Polycarbonate
Flammability rating according to UL 94	HB
Insulating material	PC
Surface characteristics	untreated

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 80 °C
---------------------------------	------------------

Mounting

Mounting type	Screw mounting
---------------	----------------

Packaging specifications

Type of packaging	none
-------------------	------

OCS PANEL 1210 PC - Mounting panel



1471786

<https://www.phoenixcontact.com/gb/products/1471786>

Classifications

ECLASS

ECLASS-13.0	27190605
-------------	----------

ETIM

ETIM 9.0	EC002779
----------	----------

OCS PANEL 1210 PC - Mounting panel



1471786

<https://www.phoenixcontact.com/gb/products/1471786>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk