






LOQUETEAUX MÉCANIQUES MECHANICAL CATCHES MECHANISCHE SCHNÄPPER	numéro number Nummer	matière material Werkstoff	décor finish Dekor	poids weight Gewicht
LOQUETEAU À GALETS SANS GÂCHE ROLLER-CATCH WITHOUT COUNTERPLATE DOPPELROLLENSCHNÄPPER OHNE SCHLIESSHAKEN A x B x C x D x E x I 53 x 14 x 3 x 15,5 x 44 x 2 Force: 1 à 1,5 kg - Resistance: 1 to 1,5 kg - Kraft: 1 bis 1,5 kg	16-1-3594	plastique	blanc	9 g
GÂCHE À POINTE COUNTERPLATE WITH POINT SCHLIESSHAKEN MIT SPITZE F x G x H 34 x 10 x 21	16-1-3595	plastique	blanc	1,5 g
GÂCHE SANS POINTE COUNTERPLATE WITHOUT POINT SCHLIESSHAKEN OHNE SPITZE F x G x H 34 x 10 x 21	16-1-3596	plastique	blanc	1,5 g



VERROUILLAGES BOLTING DEVICES VERRIEGELUNGEN	numéro number Nummer	matière material Werkstoff	décor finish Dekor	poids weight Gewicht
TARGETTE SASH BOLT SCHUBRIEGEL A x B x C x D x E 40 x 30 x 14 x 8 x 2	16-7-3680 16-7-3681	cuivre cuivre	poli chromé	66 g 66 g
VERROU À PÊNE ROND BOLT WITH ROUND SHAFT RUNDER RIEGEL A x B x C x D x E x F x G x H x I 35 x 19 x 11 x 23 x 2 x 11 x 19 x 9 x 3 * Percée et fraisurée pour vis ø 1 - Drilled and counter sunk for screws ø 1 - Gebohrt und versenkt für Schrauben ø 1	16-1-3647	acier	zingué	21 g
VERROU BOLT RIEGEL A x B x C x D x E x F x G x H x I x J 35 x 19 x 11 x 23 x 2 x 11 x 19 x 9 x 3 x 8	16-1-3430 16-1-3431	acier laiton	zingué chromé	20 g 24 g
50 x 30 x 16 x 34 x 3 x 15 x 27 x 14 x 4 x 12	16-1-3433 16-1-3434	acier laiton	zingué chromé	71 g 75 g
70 x 38 x 22 x 44 x 3,5 x 20 x 38 x 18 x 6 x 16	16-1-3436 16-1-3437	acier laiton	zingué chromé	129 g 163 g
* Percée et fraisurée pour vis ø 1 - Drilled and counter sunk for screws ø 1 - Gebohrt und versenkt für Schrauben ø 1				



avec ressort inox 304
with 304 stainless steel spring
mit Feder aus rostfreiem Stahl 304



avec ressort inox 304
with 304 stainless steel spring
mit Feder aus rostfreiem Stahl 304