

SOCKET SET (10pcs.)			
No. TB410E	kg 1	📦 1	小売参考価格 ¥10,200
ソケット(六角)	B4-08, 10, 12, 13, 14, 17, 19, 21, 22, 24		
ソケットホルダー	10コ用 EHB410		

## 12.7sq. ソケットセット [10コ組]



SOCKET SET (10pcs.)			
No. TB410XE	kg 1	📦 1	小売参考価格 ¥10,200
ソケット(六角)	B4-08, 10, 12		
ソケット(十二角)	B4-13W, 14W, 17W, 19W, 21W, 22W, 24W		
ソケットホルダー	10コ用 EHB410		

## 12.7sq. ソケットセット [10コ組]



SOCKET										
No.	S	D <sub>1</sub>	D <sub>2</sub>	H	L	ℓ	g	📦	小売参考価格	
B4-08	8	12	22	5.5	28.5	12.5	29	5	¥	750
B4-09	9	13.5	22	5.5	28.5	12.5	30	5	¥	790
B4-10	10	14.5	22	5.5	28.5	12.5	38	5	¥	790
B4-11	11	16	22	6	29	13	41	5	¥	790
B4-12	12	17	22	7.5	30.5	14.5	44	5	¥	790
B4-13	13	18.5	22	7.5	30.5	14.5	45	5	¥	790
B4-14	14	20	22	8.5	31.5	15.5	49	5	¥	790
B4-15	15	21	22	8.5	31.5	15.5	50	5	¥	830
B4-16	16	22.5	22	9	33	17	55	5	¥	830
B4-17	17	24	22	10	34	18	61	5	¥	830
B4-18	18	25	23	10	34	18	69	5	¥	830
B4-19	19	26	24	10.5	34.5	18.5	75	5	¥	830
B4-20	20	27.5	25	11	35	19	83	5	¥	890
B4-21	21	28.5	26	11.5	35.5	19.5	91	5	¥	890
B4-22	22	30	27	11.5	35.5	19.5	104	5	¥	910
B4-23	23	31	27.5	12	36	20	108	5	¥	910
B4-24	24	32.5	28.5	12	36	20	117	5	¥	910
B4-25	25	34	30.5	13	37	21	140	5	¥	1,120
B4-26	26	35	31.5	14	38	22	149	5	¥	1,120
B4-27	27	36.5	33	15	39	23	171	5	¥	1,120
B4-28	28	38	34.5	16	40	24	190	5	¥	1,360
B4-29	29	39	35.5	17	41	25	206	5	¥	1,360
B4-30	30	40	36	17	42	26	214	5	¥	1,480
B4-31	31	42	37.5	18	43	27	248	5	¥	1,630
B4-32	32	43	38.5	18	43	27	256	5	¥	1,630
B4-33	33	44	40	19	44	28	278	5	¥	1,990
B4-34	34	45	41	19	44	28	286	5	¥	1,990
B4-35	35	46	41.5	19	44	28	297	5	¥	2,490
B4-36	36	47	42.5	19	44	28	305	5	¥	2,490

## 12.7sq. ソケット(六角)

