

# AlphaTec®

ADVANCED CHEMICAL PROTECTION

## 2500 STANDARD - Model 111

Durable and breathable microporous laminate technology, Type 4/5/6 protection

Previously known as: MICROGARD® 2500 STANDARD - Model 111

### Combines exceptional mechanical strength with excellent liquid and particulate protection.

- Achieves the highest classifications for protection from biological agents in accordance with EN 14126 and ASTM F 1671 for penetration of blood, body fluids and blood-borne pathogens
- Air and water vapour permeable (breathable) fabric helps reduce the risk of heat stress
- Ultra low linting to help reduce the risk of cross contamination in critical areas
- Anti-static, tested according to EN 1149-5 & AATCC 76
- Ultrasonically welded seams provides a strong liquid and particle barrier

#### Industries

- Life Sciences
- Chemical
- Food Processing
- Industrial
- Law Enforcement

#### Applications

- Transferring liquids and solids
- Unexpected leakages spills or other releases
- Plant disinfection and sanitization
- Tank Cleaning
- Emergency Response
- Spill or leakage cleanup
- Maintenance
- Contaminated Environments



Previously known as: MICROGARD® 2500 STANDARD - Model 111

### PRODUCT INFORMATION

<b>Product Material</b>	Microporous Polypropylene Laminate non woven
<b>Design Features</b>	Coverall, 3-piece hood, elasticated hood, wrists, waist and ankles. Finger loops and single zip with resealable storm flap.
<b>Seam Type</b>	Ultrasonically welded
<b>Standards Overview</b>	CE CATEGORY III (Type 4-B, Type 5-B, Type 6-B, EN 1073-2, EN 14126, EN 1149-5)
<b>Product Reference</b>	2500 STANDARD - Model 111
<b>Weight</b>	65gsm

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 210  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### Australia

Ansell Limited  
Level 3,678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578