



EAN:	4013288236463	Size:	205x75x20 mm
Part number:	05020332001	Weight:	295 g
Article number:	6006 Joker S/L	Country of origin:	CZ
		Customs tariff number:	82041200

- The screwdriving workshop "for the pocket"
- The most common wrench sizes in one tool
- For hexagon screw heads and bolts with sizes 10-13 and 16-19 (metric) or 7/16"-1/2" and 5/8"-3/4" (imperial) and all intermediate sizes
- Self-setting double open-end spanner; return angle of only 30° when using the corner-width rectangular prisms in the jaw
- Automatically and continuously gripping hexagon screws and bolts
- Lever mechanism upon gripping prevents slipping and damage
- With mechanical ratchet functionality for fast and consistent screwdriving without removing the spanner

Self-setting double open-end spanner for hexagon screw heads and bolts with wrench sizes 10.0; 11.0; 12.0; 13.0 and 16.0; 17.0; 18.0; 19.0 (metric) or 7/16"; 1/2" and 5/8"; 11/16"; 3/4" (imperial). With its continuous and parallel jaws, the tool replaces several single wrench sizes. The required size is automatically and continuously set when attaching the tool to the hexagon bolt or screw. The integrated lever mechanism securely clamps the hexagon screw or bolt between the jaws, which significantly reduces the risk of slippage or damage. The ratchet feature ensures fast and consistent screwdriving without removing the tool. By using the corner-width rectangular prisms, a return angle of only 30° can be achieved. Ratchet feature and corner-width prism make it possible to work even in confined spaces. The adjustable Joker 6006 double open-end spanner with ratchet functionality is the universal screwdriving tool. Self-setting. Gripping. Spanning.



The screwdriving workshop "for the pocket"



The screwdriving workshop "for the pocket"



With its continuous and parallel jaws, the self-setting 6006 Joker S/L double open-end spanner replaces the most used metric and imperial single wrench sizes.

One tool for many screw sizes




With the self-setting 6006 Joker S/L double open-end wrench, you are holding the most common metric and imperial wrench sizes "in one hand".

Joker 6006: automatically and continuously self-setting



With its automatically and continuously gripping parallel jaws, the Joker 6006 double spanner covers all dimensions within the potential operative range. The tool finds the required size by itself when attaching it to the bolt or screw.

Joker 6006: gentle to the screw




The parallel, smooth jaws of the Joker 6006 double spanner offer a seating stress and can thus prevent the nut or screw head from rounding, which can occur when power is transmitted over corners.

Joker 6006: ratchet mechanism for quick working



The ratchet functionality in both jaws of the double spanner ensures fast and consistent screwdriving without removing the tool.

Joker 6006: low return angle



Thanks to the corner-width rectangular prisms in both jaws of the double spanner, a return angle of only 30° can be achieved.

Further versions in this product family:

							
	mm	inch	mm	inch	mm	mm	mm
05020332001	10.0; 11.0; 12.0; 13.0	7/16"; 1/2"	16.0; 17.0; 18.0; 19.0	5/8"; 11/16"; 3/4"	10	14.0	208.6

Web link

<https://www.wera.de/en/05020332001>

Wera - 6006 Joker S/L
05020332001 - 4013288236463

Wera Werkzeuge GmbH
Korzerter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de