

Cable Ties with Raster Locking and Coating : MAT16SSC7

Stainless Steel Cable Tie with Raster Locking and Coating 430x7.0 mm black

Article number: 111-92162

 Add to watchlist



 Images (3)



Features

- MAT ties are similar to conventional 'plastic' cable ties
- Work on ratchet system
- Available in type 316 stainless steel

Certifications & Approvals

HF ✓ LFH ✓ RoHS ✓

Application

The MAT range of stainless steel cable ties can be used in the most arduous of conditions or where the additional security, strength and fire resistance of a metal fixing is required. Used in all industries from Mass Transit, Ship building, oil rigs, mining, & chemical to theatres and exhibition halls. In the event of a fire, cables will remain securely held in place and will not fall to block emergency exits.

More products in this product group [Contact](#) 

Base Data



Application Tool	KST-STG200, MK9SST, MK9PSST
Colour	Black (BK)
Identification Plate Position	none
Pack Cont.	100 pcs.
Package Content in	bag
PART DESCRIPTION	MAT16SSC7-SS316/SP-BK
Product Family	MAT-C
Product Group	Cable Ties with Raster Locking and Coating
Releasable Closure (Yes/No)	No
Short Description	Stainless Steel Cable Tie with Raster Locking and Coating 430x7.0 mm black
Tie Closure	ladder style
Variant	No Serration

Product Dimensions



Bundle \varnothing max.	120 mm
Bundle \varnothing min.	10.0 mm
Length (L)	430 mm
Min.Tensile Strength	445 N
Thickness (T)	0.40 mm
Width (W)	7.0 mm

Material and Specifications



ELV compliant (Article 4 - 2)	YES
Flammability	non-burning (except coating)
Halogenfree	Yes
Hazardous good	No
Limited Fire Hazard	Yes
Material	Stainless Steel (SS316), Polyester (SP)
Operating Temperature - °C	-80 °C to +538 °C
Operating Temperature Coating	-50 °C to +150 °C

Specifications

[Contact](#)

Logistics and Packaging



More Information



ETIM 7.0 Key

EC000046

Accessories



KST-STG200

110-09950

Manual tensioning tool for metal ties
MBT-Series



MK9SST

110-95000

Manual tensioning tool for metal ties
MBT-Series



MK9PSST

110-95350

Pneumatic tensioning tool for metal
ties MBT-Series



Similar products



MAT12SSC7

111-96120

Cable Ties with Raster Locking and
Coating



MAT8SSC5

111-92003

Cable Ties with Raster Locking and
Coating



MAT8SSC7

111-92004

Cable Ties with Raster Locking and
Coating



MAT24SSC7

111-92200

Cable Ties with Raster Locking and
Coating



Contact 

© HellermannTyton 2022