

IMPACT SERIES

9531 Low Cut Laced Shoe



KING'S

by Honeywell

The Logical Choice



Description: Leather Low Cut Laced Shoe

Size: EU 35-48 | UK 3-13

Application: Construction, Building and Maintenance Services, Manufacturing, Food Industries, Transportation and Logistics, Shipbuilding Industry, Telecoms and Utilities.

Standard: CE EN 20345:2011

Certification: S3 SRC



SKU	Steel Midsole	Color	Outsole
9531-XX/XX	Yes	Black	Double Density PU

To specify size, replace 'XX/XX': 9531-{EU size}/{UK size}

The King's IMPACT Series offers a comfortable fit and value in a professional safety shoe. Available in all standard sizes, the 9531 Low Cut Laced Shoe provides long-term durability and ensures adequate protection for a variety of industrial environments. It features a lightweight and anti-slip PU sole that provides a good grip on various work surfaces.

Features:

- Resistant to oils, acids and alkalis
- 200 J - Impact resistant carbon steel toe cap
- Puncture resistant steel midsole insert
- Lightweight, slip resistant, dual density polyurethane (PU) sole
- Provides impact cushioning for the whole foot
- Ergonomic and comfort EVA for the entire foot
- Anti-static
- Water resistant leather

Industry Applications:

- Recommended for indoor/outdoor works. Suitable for medium or light industries.

Storage And Care:

- Footwear should be stored in their original packaging. Keep in an area that is not subject to rapid changes in temperature or humidity levels.

Care Instructions:

- Store shoes in a cool, dry and well-ventilated area after use.
- Remove excess dust or dirt with a brush.
- Remove any marks using a damp cloth and soap if necessary. Polish any grain or pigmented leathers using a commercially available shoe care product.

SOLE FEATURES



Anti-Static



Slip Resistant



Mineral Oils Resistant



Organic Oils & Fats Resistant



Puncture Resistant

TOECAP FEATURES



Steel Safety Toecap

COMFORT FEATURES



Breathable Lining



Comfort Footbed



Impact Absorption



Lightweight

SPECIAL FEATURES



Water Resistant Leather

 **King's by Honeywell**
Honeywell Safety and Productivity Solutions
Level 25, UOA Corporate Tower Lobby B,
Avenue 10, The Vertical
59200 Bangsar South City
Kuala Lumpur, Malaysia

 +603-2777 3948

 hsp.asean@honeywell.com

 sps.honeywell.com

LEARN MORE



IMPACT 9531 | v10/24
© 2024 Honeywell International Inc.