

V-Gard® Chinstraps

Technical Datasheet



Key Features

- Complete range of reliable, comfortable and adjustable chinstraps for use along with V-Gard & ThermalGard Safety helmets.
- A variety of designs to accommodate the varied conditions of use with options depending on the environment and the encountered risks.

*Never attempt to use chinstraps from another manufacturer.
There is no approved cross-combination with other chinstrap/helmet manufacturer.*

Please note that V-Gard H1 chinstraps are only approved with V-Gard H1 helmets.



V-Gard Universal 4-point Chinstrap

- Compatible with all MSA V-Gard and ThermalGard safety helmets*
- Easy mounting directly on Push-Key or Fas-Trac® III suspensions
- Adjusters for better size setting
- Compatible with helmet-mounted ear defenders
- Very comfortable soft & narrower black strap OEKO-TEX® certified
- No metallic parts for a use in electrical applications
- Optional: chin cup made with arc flash resistant material

**except V-Gard H1*



Thermalgard 4-point Textile Chinstrap

- Compatible with Thermalgard safety helmet
- Easy mounting on Fas-Trac® III suspension
- Specific OEKO-TEX® webbing with low thermal conductivity for high temperature environments (steel mills, foundries...)
- Wide range of adjustments for optimum comfort and fit
- Orange opening buckle for quick identification
- No metallic parts



V-Gard H1 4-point chinstraps

- Integrated rescue whistle
- Mounting on the shell
- Very comfortable strap
- 2 side brackets for easy & quick adjustment
- 2 chinstraps:
P/N 10194765 for V-Gard H1 Trivent (EN12492)
P/N 10194766 for V-Gard H1 Novent (EN397)



V-Gard 4-point Textile chinstrap

- Compatible with V-Gard 520 and on request with V-Gard 500
- Zebra design



V-Gard 2-point Textile chinstrap

- Mounting on the shell
- Zebra design
- Adjuster for better size settings
- No metallic parts for a use in electrical applications



V-Gard 2-point Elastic chinstrap

- Mounting on the shell
- Better flexibility : Can be worn on the top of the helmet when not used
- No metallic parts for a use in electrical applications



V-Gard® Chinstraps

Technical Datasheet





Technical Specifications


Material	
V-Gard® Universal 4-point Textile chinstrap	Textile: Polyester webbing Color: black strap OEKO-TEX® certified and grey male buckle for a quick identification Width: 15 mm
Thermalgard 4-point Textile chinstrap	Textile : Modacrylique Polyester webbing Color: black OEKO-TEX® certified strap and orange opening buckle Width: 16 mm
V-Gard H1 4-point textile chinstraps	Textile : Polyester webbing Color: grey (10194766 - 4 point chinstrap for V-Gard H1 Novent helmets) or black (10194765 - 4 point chinstrap for V-Gard H1 trivent helmets) Width : 15 mm
V-Gard 2 and 4-point "standard" Textile chinstrap	Textile: Polyester interweaved webbing Colour: Zebra stripes Width: 18 mm
V-Gard 2-point elastic chinstrap	Webbing elastic Colour: Black Width: 19 mm
Adjusters (all models)	PA
Hooks / Clips (all models)	POM
Ring (4-point "standard" chinstrap)	Metal
Approvals	
Standards	CE Certified (EN397) with MSA Industrial Helmets V-Gard H1 4-point chinstrap (P/N 10194765) is CE certified (EN12492) with V-Gard H1 Trivent helmet
General	
Weight	V-Gard Universal 4 point textile: 46 g Thermalgard 4-point textile : 46 g 4 point textile: 25 g 2 point elastic: 15 g 2 point textile: 10 g V-Gard H1 Novent 4 point textile: 34 g V-Gard H1 Trivent 4 point textile: 38 g
Packaging	P/N = 1 chinstrap but sold as bag of 20 units (Except V-Gard H1 4 point chinstraps which are sold by unit)

Ordering Information

Part No.	Description	Minimum/ Multiple of order	MSA Industrial Helmets compatibility
GA90047	V-Gard Universal 4-point Textile chinstrap	Bag of 20 units	All V-Gard & ThermalGard family helmets, except V-Gard H1
GA90063	Thermalgard 4-point Textile chinstrap	Bag of 20 units	Thermalgard
10194766	V-Gard H1 Novent 4-point chinstrap	1 unit	V-Gard H1 Novent
10194765	V-Gard H1 Trivent 4-point chinstrap	1 unit	V-Gard H1 Trivent
10148055	V-Gard 4-point textile chinstrap	Bag of 20 units	V-Gard 520 and V-Gard 500 (on request, extra-cost)
9100001	V-Gard 2-point textile chinstrap	Bag of 20 units	All V-Gard and ThermalGard family helmets, except V-Gard H1
B0259378	V-Gard 2-point textile elastic chinstrap	Bag of 20 units	V-Gard, V-Gard 200, V-Gard 500 & V-Gard 520
GA90040	Chincup	1 unit	All V-Gard and ThermalGard family helmets (except V-Gard H1), with V-Gard Universal 4-point chinstrap (GA90047)



GA90047



GA90063



GA90040



10194765



10194766



10148055



9100001



B0259378