

# Terminal Blocks, Linergy, plugin bridge jumper, for 5.2mm wide blocks, 10 points, grey

NSYTRAL210GR

Product availability: Stock - Normally stocked in distribution facility

#### Main

Range	Linergy	
product name	Linergy TR	
Product or Component Type	Plug-in bridge	
Device short name	TRA	
Accessory / separate part category	Connection accessory	
Product compatibility	TRV screw terminal terminal block TRP push-in terminal block TRR spring terminal terminal block TRH IDC terminal block	
Number of ways	10 ways	

## Complementary

Cable cross section	0.004 in² (2.5 mm²)	
number of connections	2	
	3	
	4	
Number of measurement input	6	
	2	
	1	
	4	
	3	
Quantity per Set	Set of 10	
Net Weight	0.3 oz (9 g)	
color	Gray	

# Ordering and shipping details

Category	US10CP521715	
Discount Schedule	0CP5	
GTIN	3606480534119	
Returnability	Yes	
Country of origin	DE	

## **Packing Units**

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.39 in (1.000 cm)

Price is "List Price" and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Package 1 Width	5.91 in (15.000 cm)	
Package 1 Length	3.15 in (8.000 cm)	
Package 1 Weight	0.282 oz (8.000 g)	
Unit Type of Package 2	BB1	
Number of Units in Package 2	10	
Package 2 Height	0.39 in (1.000 cm)	
Package 2 Width	5.91 in (15.000 cm)	
Package 2 Length	6.30 in (16.000 cm)	
Package 2 Weight	3.034 oz (86.000 g)	
Unit Type of Package 3	S01	
Number of Units in Package 3	400	
Package 3 Height	5.91 in (15.000 cm)	
Package 3 Width	5.91 in (15.000 cm)	
Package 3 Length	15.75 in (40.000 cm)	
Package 3 Weight	8.073 lb(US) (3.662 kg)	



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

#### **Use Better**

Packaging made with recycled cardboard	Yes
Packaging without single use plastic	No
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
REACh Regulation	REACh Declaration
Halogen content performance	Halogen free plastic parts product

#### **Use Again**

○ Repack and remanufacture	
Circularity Profile	No need of specific recycling operations
Take-back	No