

# MASTER LED Spot DimTone

MAS LEDspotMV VLE CLA DT 5-50W GU10 36D



DimTone takes dimming to an exciting next level with a beautiful, sunset-like effect. As the light is dimmed, DimTone reduces the color temperature from 2700 to 2200 K. This creates a warm, intimate ambience at low light levels, with the same effect as dimmed halogens or incandescent lamps. So hotel, bar, restaurant and home owners can take advantage of energy-saving LED lighting and still create a natural, cozy ambience.

## Product data

### • General Information

Cap-Base	GU10
Bulb Shape	PAR16 [ PAR 2 inch]
Nominal Lifetime (Nom)	25000 h
Switching Cycle	50000X
B50L70	25000
Technical Type	5-50W

### • Light Technical

Color Code	822-827 [ tunable warm white]
Beam Angle (Nom)	36 °
Luminous Intensity (Nom)	600 cd
Color Designation	Warm White (WW)
Rated Beam Angle	36 °
Correlated Color Temperature (Nom)	2200-2700 K
Luminous Efficacy (rated) (Nom)	69 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Luminous Flux In 90° Cone (Rated)	345 lm

### • Operating and Electrical

Power (Rated) (Nom)	5 W
Lamp Current (Nom)	28 mA
Wattage Equivalent	50 W
Starting Time (Nom)	0.5 s

Warm Up Time To 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.7
Voltage (Nom)	220-240 V

### • Temperature

T-Case Maximum (Nom)	80 °C
----------------------	-------

### • Controls and Dimming

Dimmable	Yes
----------	-----

### • Approval and Application

Energy Saving Product	Yes
Suitable For Accent Lighting	Yes
Energy Efficiency Label (EEL)	A+
Energy Consumption kWh/1000 h	5 kWh

### • Product Data


Full product code	871869666762000
Order product name	MAS LEDspotMV VLE CLA DT 5-50W GU10 36D
EAN/UPC - Product	8718696667620
Order code	929001278602
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929001278602

# PHILIPS

# MASTER LED Spot DimTone

Net Weight (Piece) 0.036 kg

## Dimensional drawing



GU10 230V 5W-50W 350lm 36D 2700K dim


Product

MAS LEDspotMV VLE CLA DT 5-50W GU10 36D


Accent Lighting - Spots

GU10 5W 2700K 36D 9290012786

1 x 345 lm



# MASTER LED Spot DimTone



© 2016 Philips Lighting Holding B.V.  
All rights reserved.

Specifications are subject to change without notice. Trademarks are the property of Koninklijke Philips N.V. (Royal Philips) or their respective owners.

[www.philips.com/lighting](http://www.philips.com/lighting)

2016, September 8  
data subject to change