


Features

- For use with article 100390 Electric Screwdriver
- Head types are Phillips, Torx & Slotted
- Sizes are PH1, PH2, T10, T20, SL3 & SL4
- Material: S2 alloy steel
- Exquisite workmanship, each edge can be accurately locked screws, no damage to the screw and the screwdriver head.
- Suitable for electric screwdriver, hand screwdriver, electric drill and other tools

RS PRO 10pcs Screwdriver Bits 4mm dia x 40mm Overall Length



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO Screwdriver Bits

4.0mm dia. X 40mm L

The screwdriver bit chuck size is 4mm for use with RS PRO Electric Screwdriver (Article 100390)

Features and Benefits

- Head Types are Phillips, Torx and Slotted
- Sizes are PH1, PH2, T10, T20, SL3 & SL4
- High quality bit is supported by precise cutting and heat treatment
- The bits are equipped with 4mm shank drive that work with wide variety of small torque controlled electric screwdriver

General Specifications

Head Type	See details below
Type	Driver Bit
Size	See details below
Material	S2 alloy steel
Overall Length	40mm
Drive Size	See details below
Qty of Pack	10pcs

Stock No.	Product Name	Head Type	Size	Drive Size
0630907	Screwdriver Bit	Phillips	PH1	4mm dia
0630908	Screwdriver Bit	Phillips	PH2	4mm dia
0630909	Screwdriver Bit	Torx	T10	4mm dia
0630911	Screwdriver Bit	Torx	T20	4mm dia
0630912	Screwdriver Bit	Slotted	SL3	4mm dia
0630913	Screwdriver Bit	Slotted	SL4	4mm dia

Approvals

Declarations	REACH DoC
--------------	-----------

Similar Products

Stock No.	Brand	Product Name	Size	Head Type	Size	For Use With
0630907	RS PRO	Screwdriver Bits	4.0mm dia x 40mm L	Phillips	PH1	Article 100390 Electric Screwdriver
0630908	RS PRO	Screwdriver Bits	4.0mm dia x 40mm L	Phillips	PH1	Article 100390 Electric Screwdriver
0630909	RS PRO	Screwdriver Bits	4.0mm dia x 40mm L	Torx	T10	Article 100390 Electric Screwdriver
0630911	RS PRO	Screwdriver Bits	4.0mm dia x 40mm L	Torx	T20	Article 100390 Electric Screwdriver
0630912	RS PRO	Screwdriver Bits	4.0mm dia x 40mm L	Slotted	SL3	Article 100390 Electric Screwdriver
0630913	RS PRO	Screwdriver Bits	4.0mm dia x 40mm L	Slotted	SL4	Article 100390 Electric Screwdriver

Φ4*40*3.0*PH1



Φ4*40*4.0*PH2



Φ4*40*3.0MM



Φ4*40*4.0MM



Φ4*40*T10



Φ4*40*T20

