

Features

- Spotlight & floodlight modes
- Super bright 1000 lumen floodlight
- Strong magnetic stand
- Useful carabiner clip so the light can be hung
- USB-C rechargeable

RS PRO LED Compact Folding Work Light, 1000 lm

RS Stock No.: 0143263



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

RS PRO LED Work Light, 1000 Lumens, Rechargeable

1000 Lumen white COB LED, 6500k
With 300 Lumen 6500k CREE LED top torch
Super tough copolymer & aluminium construction
Glow-in-the-dark strip around reflector for extra visibility
180° Adjustable stand/handle with strong magnets
Spring loaded carabiner hook on the stand
1m high quality USB Type-C charging cable (included)
Fast 5V 2A USB Type-C charging - 3.5 hours charge time

General Specifications

Lamp Type	LED
Luminosity	1000 lm
Length	130 mm
Mains Plug Type	USB
Rechargeable	Yes

Mechanical Specifications

USB	Type-C 5V 2A charging
Battery Charge Time	3.5 hours
Cable	1m charging cable included
Battery	3.7v 'LG' 5200mAh Li-ion battery
Dimensions	Folded H 130 x W 56 x D 48mm extended H 241.5 x W 56 x D 40mm
Weight	325g
Operation	Floodlight:- High - 1000LM - 3 hrs > Medium - 450LM - 6.5 hrs > Low - 40LM - 82 hrs > Off Flashlight:- High - 300LM - 12 hrs > Low - 80LM - 46 hrs > Off [When ON in either Flashlight or Floodlight, press and HOLD the button to switch to the other mode] [If left in any mode for over 3 seconds, the next press will turn off]

Approvals

Declarations	EMC RoHS REACH
Standards Met	BS EN IEC 55015:2019/A11:2020 BS EN 61547:2009 BS EN IEC 61000-3-2:2019 BS EN 61000-3-3:2013/A1:2019 IEC 62321 IPX5 IEC 62133

Similar Products

Stock No.	Brand	Product Name	Luminosity	Rechargeable	Mains Plug
0143263	RS PRO	LED Inspection Lamp	1000 lm	Yes	USB
0143257	RS PRO	LED Inspection Lamp	1300 lm	Yes	USB
111-7927	RS PRO	LED Inspection Lamp	White 5700K	Yes	Type C - Europlug
111-7926	RS PRO	LED Inspection Lamp	White 5700K	Yes	Type G - British BS1363
183-5235	RS PRO	LED Inspection Lamp		Yes	USB
186-4628	RS PRO	LED Inspection Lamp	700 lm	Yes	USB
186-4626	RS PRO	LED Inspection Lamp	400 lm	Yes	USB
255-4202	RS PRO	LED Inspection Lamp	720 lm	Yes	USB
186-4627	RS PRO	LED Inspection Lamp	300 lm	Yes	USB
171-8488	RS PRO	LED Inspection Lamp	300 lm	Yes	Type G - British BS1363, USB