

## Features

- Round jaws taper to a super fine nose, just 0.8 mm (+/- 0.1 mm) diameter.
- Jaws move in parallel throughout use.
- Smooth jaws to prevent damage to workpiece.
- Jaws case hardened to HRC 57 and chemically blackened for durability.
- Zinc-plated handles with detailing for added grip.

## RS PRO Fine Nose Round Jaws Parallel Plier 125 mm

RS Stock No.: 0434621



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

Buy this product from <https://uk.rs-online.com/>

## RS PRO Fine Nose Round Jaws Parallel Plier

A unique parallel plier with exceptionally fine nosed jaws for delicate working or in restricted space.

The round jaws taper to a fine nose, just 0.8 mm (+/- 0.1 mm) across. Perfect for working in compact machinery, for shaping tight loops and bends in shim and similar materials. Uniquely, these fine nose pliers also benefit from jaws that always move in parallel. Grip anywhere along the length of the smooth jaws without risk of damaging your workpiece.

### Benefits

- Grip the smallest or most difficult to access items between fine nose jaws.
- Use for bending and forming loops with soft metals.
- Make consistently sized loops of varying diameters.
- Parallel jaws grip securely along their whole length.
- Work without fear of marking or damaging your workpiece.
- Built to last, with a robust construction and rust-resistant finish.

### Applications

This tool has been developed to provide a firm grip in the smallest spaces, ideal for:

- Engineers working with compact machinery.
- Horologists and jewellers.
- Model Builders.

## General Specifications

Plier Type	Fine Nose Round Jaws Parallel Plier
Number of Pieces	1
Overall Length	125mm
Cutting Capacity	N/A
Material	Steel jaws and zinc-plated steel handles.
ESD Safe	No
Jaw Tip Diameter	0.8 mm (+/- 0.1 mm)
Jaw Opening	11mm
Non Sparking	No
Height Safe	No

## Approvals

Declarations	REACH DoC
--------------	-----------

## Similar Products

Stock No.	Brand	Product Name	Jaw Opening	Parallel	Overall Length
0606317	RS PRO	CENTRE CONDUCTOR CUTTING NIPPER	Up to 25 mm (Duct Rod Ø)	No	110 mm
0606320	RS PRO	Bullet & Snap Connector Insert Tool	46mm	No	145mm
0606319	RS PRO	Spanner Quick Grip	25 mm Max	No	135mm
0606316	RS PRO	Security Crimping and Cutter Plier	0.9mm (Ø cables)	No	212mm
0434623	RS PRO	Snipe Nose Serrated Jaws Parallel Plier	10mm	Yes	125mm
0606318	RS PRO	Snipe Nose Smooth Jaws Parallel Plier	10mm	Yes	125mm
0434621	RS PRO	Fine Nose Round Jaws Parallel Plier	11mm	Yes	125mm
0606312	RS PRO	Fine Clamping Plastic Jaws Parallel Plier	20mm	Yes	168mm
0434622	RS PRO	Flat Nose Nylon Jaws Parallel Plier	10mm	Yes	140mm
0441178	RS PRO	Side Cutter Parallel Plier for Hard Wire 125mm	10mm	Yes	125mm
0606314	RS PRO	Side Cutter Parallel Plier for Hard Wire 160mm	14mm	Yes	167mm
0606313	RS PRO	Side Cutter Parallel Plier for Hard Wire 140mm	8mm	Yes	140mm
0434617	RS PRO	Side Cutter Parallel Plier for Hard Wire 140mm, w/ Grip Handle	8mm	Yes	140mm

