

# SACC-FP-M-M8/PRESS SMD - Housing screw connection



1412500

<https://www.phoenixcontact.com/in/products/1412500>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Housing screw connection, Pin, M8, Front mounting, Alternative product in accordance with RoHS II without Exemption 6c (Pb < 0.1 %) item no.: 1239000

## Your advantages

- Reduced mounting costs thanks to two-piece device connector
- Easy device integration, thanks to mechanical port screw connections with press-in contour
- Efficient PCB assembly: two-piece connectors for SMT soldering

## Commercial data

Item number	1412500
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	ABQ
Product key	ABQHAC
GTIN	4046356989091
Weight per piece (including packing)	4.2 g
Weight per piece (excluding packing)	4.2 g
Customs tariff number	74198090
Country of origin	DE

# SACC-FP-M-M8/PRESS SMD - Housing screw connection



1412500

<https://www.phoenixcontact.com/in/products/1412500>

## Technical data

### Product properties

Product type	Panel mounting base
Thread type	M8

### Material specifications

Material	Brass, nickel-plated
----------	----------------------

### Connector

#### Connection 1

Head design	Pin
Head thread type	M8

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection (when plugged in)	IP67 (correctly plugged in and locked)
Degree of protection	IP67 (correctly plugged in and locked)

### Mounting

Mounting type	Front mounting Press-in mounting
Assembly note	Press-in mounting

# SACC-FP-M-M8/PRESS SMD - Housing screw connection



1412500

<https://www.phoenixcontact.com/in/products/1412500>

## Classifications

### ECLASS

ECLASS-11.0	27440224
ECLASS-12.0	27440224
ECLASS-13.0	27440224

### ETIM

ETIM 9.0	EC003556
----------	----------

### UNSPSC

UNSPSC 21.0	39121100
-------------	----------

# SACC-FP-M-M8/PRESS SMD - Housing screw connection



1412500

<https://www.phoenixcontact.com/in/products/1412500>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	6(c)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	4e3862ce-6ab5-42c3-8176-dfa3c226089d

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)