

# Product datasheet

Specifications



## green plain cap I for flush mounted push button

Local distributor code:

407818824

ZBAF331

**EAN Code: 3606481361806**

### Main

Range of product	Harmony XB4 Harmony XB5
Accessory / separate part category	Marking accessory
Accessory / separate part type	Marked push-button cap
Product compatibility	ZB4FA0 ZB5FA0
Accessory / separate part destination	Push-button head
User language	International
Marking	White I on green background
Cap/operator or lens colour	Green
Shape of signaling unit head	Round
Quantity per set	Set of 1
Sale per indivisible quantity	10
Net weight	0.001 kg

### Complementary

Range compatibility	Harmony XB4 Harmony XB5 Harmony XAL
Operator profile	Flush
Main group	Push-button

### Environment

Standards	ISO 21702 ISO 22196:2011
-----------	-----------------------------

### Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.3 cm
Package 1 Width	5.3 cm
Package 1 Length	5.5 cm
Package 1 Weight	2.0 g
Unit Type of Package 2	CAR

---

<b>Number of Units in Package 2</b>	10
<b>Package 2 Height</b>	5.5 cm
<b>Package 2 Width</b>	4.3 cm
<b>Package 2 Length</b>	5.2 cm
<b>Package 2 Weight</b>	20.0 g

---

## **Contractual warranty**

---

<b>Warranty (in months)</b>	18
-----------------------------	----

## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

Total lifecycle Carbon footprint 1

Environmental Disclosure [Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard Yes

Packaging without single use plastic Yes

[EU RoHS Directive](#) Pro-active compliance (Product out of EU RoHS legal scope)

REACH Regulation [REACH Declaration](#)

## Use Longer

### Lifetime extension

Repair No

## Use Again

### Repack and remanufacture

End of life manual availability [End of Life Information](#)

Take-back No

Offer Marketing Illustration

Product benefits / Features

---

### Features Harmony XB5



- 

Quick and easy assembly and disassembly
- 

Excellent mechanical connection with operator head
- 

Various types of connection: screw clamp, connector, Faston connector, spring terminal, or printed circuit board
- 

Large set of accessories to customize your panels
- 

Robustness to withstand harsh environments

Offer Marketing Illustration

Product benefits / Features

---

## Technical Benefits

Harmony XB5

Conformity with IEC, UL, CSA, CCC EAC, and JIS standards, as well as CE marking and marine approvals

Up to IP66, 67, 69, 69K, and type 4X protection ratings

High vibration resistance with shake-proof terminal screws



Operating temperature from -40°C to 70°C

Shock protection level up to IK06

Secure switching of inductive or heavy DC loads directly – 100 000 operations at 10A, 24V dc

Image of product / Alternate images

Alternative

---





