

HC-B 32-SD-FQU/FS - Protective cover



1646120

<https://www.phoenixcontact.com/in/products/1646120>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective cover B32, for double locking latch, protective cover material: PA, height: 90.6 mm, seal: no, with lanyard

Commercial data

Item number	1646120
Packing unit	10 pc
Minimum order quantity	1 pc
Sales key	BF7
Product key	AF7AAZ
Catalog page	Page 655 (C-2-2017)
GTIN	4017918927301
Weight per piece (including packing)	36.38 g
Weight per piece (excluding packing)	35.61 g
Customs tariff number	85389099
Country of origin	DE

HC-B 32-SD-FQU/FS - Protective cover



1646120


<https://www.phoenixcontact.com/in/products/1646120>

Technical data

Product properties

Product type	Protective cover
Housing type	Protective cover
Type	B32
Type	for supporting base element with double locking latch
Retaining cord present	yes
Seal present	no

Dimensions

Dimensional drawing	
Width	96.5 mm
Height	90.6 mm
Length	18 mm
Diameter	30 mm

Material specifications

Material Protective cover	PA
Flammability rating according to UL 94	HB
Material, protective cover	PA

Mechanical properties

Mechanical data

Locking type	Pin
--------------	-----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP54
Ambient temperature (operation)	-20 °C ... 100 °C

Mounting

Assembly note	Plastic protective cover for short-term protection
---------------	----------------------------------------------------

HC-B 32-SD-FQU/FS - Protective cover




1646120

<https://www.phoenixcontact.com/in/products/1646120>

Drawings

Dimensional drawing



Dimensional drawing

HC-B 32-SD-FQU/FS - Protective cover



1646120

<https://www.phoenixcontact.com/in/products/1646120>

Classifications

ECLASS

ECLASS-11.0	27440208
ECLASS-12.0	27440208
ECLASS-13.0	27440208

ETIM

ETIM 9.0	EC002314
----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

HC-B 32-SD-FQU/FS - Protective cover



1646120

<https://www.phoenixcontact.com/in/products/1646120>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.
A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420
info@phoenixcontact.co.in