



**3 YEAR  
WARRANTY**



## Datasheet

# RS PRO LCD Desoldering Station

Stock number: 137-2292

EN

### Large LCD display

Quick and easy to set the desired temperature and check the actual temperature.

### Microprocessor Controlled

Microprocessor Controlled, provides accurate temperature control from 160 to 480°C.

### High power desoldering tool with vacuum

Designed with a quality Ceramic heating element and built-in high power 600mmHg air pump, particularly for lead-free desoldering of multilayer boards.

Vacuum indicator

Solder collector lock

**140W  
480°C**

Desoldering gun holder, with sponge

### Efficient operation, quick and easy

Ergonomically friendly structure allows one hand operation, only takes a few seconds per pin, more safe, efficient and comfortable.



## Specifications:


Model Number	137-2292
Plug type	F and G
Primary Application Category	Soldering
Input Voltage	220~240V ~50Hz
Power Consumption	140W
Soldering Power	90 W
Heating Element	Ceramic Heater
Temperature Range	160°C - 480°C
Vacuum Pressure	>600 mm Hg
Start Up Time	0 to 160°: 30 seconds. 0 to 300°C: 60 seconds.
Nozzle	Φ1.2 mm (on the gun) / Φ1.0 mm / Φ1.5 mm
Display Type	LCD
Height	172 mm
Width	135 mm
Depth	190 mm
Weight	1.6 kg

## EU F schuko & UK G type Plug



## Contents List:

**Desoldering Station**  
**3 x Cleaning Tools**  
**4 x Filter Sponges**  
**2 x Power Cords (UK Type G Plug and Euro Type F Plug)**  
**User Manual**  
**Desoldering Gun**  
**Soldering Stand**  
**3 x Nozzles: 1.0 mm, 1.2 mm and 1.5 mm diameter**  
**Soldering Iron Tip (Conical)**



## Features:

**It is a thermostatically controlled desoldering station that provides high performance. Ergonomically friendly structure allows one hand operation, only takes a few seconds per pin, more safe, efficient and comfortable.**

**Efficient desoldering tool with a built-in vacuum for through-hole boards and components.**

**Microprocessor Controlled, provides accurate temperature control from 160 to 480°C.**

**The ceramic heater features 20 times longer lifetime and better performance than traditional type heater**

**Designed with a quality heating element, it provides higher performance and longer lifetime than traditional type. Built-in high power 600 mmHg air pump, particularly for lead-free desoldering of multilayer boards.**

**Ergonomically friendly structure allows one hand operation, only takes a few seconds per pin, more safe, efficient and comfortable.**

**Quick and easy to set the desired temperature and check the actual temperature.**

**Fahrenheit or Celsius unit selection.**

**Large LCD display**

**Complies with CE standard. Conform to RoHS.**

**[rspro.com](http://rspro.com)**

**Replacement Accessories:**

<b>RS Part no.</b>	<b>Description</b>
<b>137-2293</b>	<b>Cleaning tool for 137-2292</b>
<b>137-2294</b>	<b>De-soldering gun for 137-2292</b>
<b>137-2295</b>	<b>Filter sponge x 4 (ø20.8x1+ø16.8x3) for 137-2292</b>
<b>137-2296</b>	<b>Replacement Nozzle for 137-2292</b>