

F202 A-25/0,03 AP-R



F202 A-25/0,03 AP-R Residual Current Circuit Breaker

General Information

Extended Product Type	F202 A-25/0,03 AP-R
Product ID	2CSF202401R1250
EAN	8012542785101
Catalog Description	F202 A-25/0,03 AP-R Residual Current Circuit Breaker
Long Description	The RCCBs F200 series assures protection to people and installations against fault current to earth. A large offer for standard instantaneous and selective AC and A types is completed with some configurations for special applications. This product provides the best compromise between safety and continuity in the service, thanks to the resistance to unwanted trippings.

Ordering

Minimum Order Quantity	1 piece
Customs Tariff Number	85363030

Popular Downloads

Data Sheet, Technical Information	9AKK107046A0424
Instructions and Manuals	Manual sheet inside the box

Dimensions

Product Net Width	0.035 m
Product Net Height	0.085 m
Product Net Depth / Length	0.069 m
Product Net Weight	0.200 kg

Technical

Standards	IEC/EN 61008 UL 1053
Operating Characteristic	Instantaneous (APR High Immunity)
Type of Residual Current	A type
Rated Residual Current	30 mA
Rated Current (I_n)	25 A
Number of Poles	2
Power Loss	at Rated Operating Conditions per Pole 1 W

Rated Voltage (U _r)	230/400 V
---------------------------------	-----------

Environmental

Ambient Air Temperature	Operation -25 ... +55 °C Storage -40 ... +70 °C
RoHS Status	Following EU Directive 2011/65/EU

Technical UL/CSA

Maximum Operating Voltage UL/CSA	277 V AC
----------------------------------	----------

Certificates and Declarations (Document Number)

Declaration of Conformity - CE	9AKK106713A5602
Environmental Information	Refer to RoHS
Instructions and Manuals	Manual sheet inside the box
RoHS Information	2CSC423001K2702

Container Information

Package Level 1 Units	1 piece
Package Level 1 Width	0.041 m
Package Level 1 Height	0.078 m
Package Level 1 Depth / Length	0.096 m
Package Level 1 Gross Weight	0.225 kg
Package Level 1 EAN	8012542785101

Classifications

Object Classification Code	Q
E-nummer	2160175
ETIM 4	EC000003 - Residual current circuit breaker (RCCB)
ETIM 5	EC000003 - Residual current circuit breaker (RCCB)
ETIM 6	EC000003 - Residual current circuit breaker (RCCB)
ETIM 7	EC000003 - Residual current circuit breaker (RCCB)

Categories

Low Voltage Products and Systems → Modular DIN Rail Products → Residual Current Devices RCDs → Residual Current Devices RCDs

