



Chemical protection

# ULTRANEО 401

Splashes | intermittent wear

Tactile sensitivity for light chemical protection



CHEMICAL PROTECTION  
**TYPE A**

EN388



2110X

EN ISO 374-1



TYPE A  
ALMNST

EN ISO 374-5



CATEGORY 3



0334

DEXTERITY

EN420:  
5/5

## SPECIFIC ADVANTAGES



### Comfort

- Added comfort and absorption of perspiration, due to the cotton flock-lining
- Great dexterity, due to the gloves reduced thickness



### Productivity

- Good grip on slippery objects, due to the embossed texture



### Care for the environment

- Plastic packaging optimized, Recycled packaging
- Recycled material in the packaging: 30 %

## INDUSTRIES

- Automotive/mechanical industry
- Other industries

## APPLICATIONS

- Industrial cleaning, maintenance
- Preparation of industrial glues
- Battery manufacturing
- Spray-painting



Chemical protection

# ULTRANEО 401

Splashes | intermittent wear

## LEGENDS

EN388	MECHANICAL HAZARDS
2 1 1 0 X	PERFORMANCE LEVELS (X = NOT TESTED)
0-4 0-5 0-4 0-4 A-F P	
	Impact protection (optional)
	Cut resistance according to ISO 13997
	Puncture resistance
	Tear resistance
	Blade cut resistance
	Abrasion resistance
EN ISO 374-1	CHEMICAL RISKS
TYPE A	A: Methanol L: Sulphuric acid 96% M: Nitric acid 65% N: Acetic acid 99% S: Hydrofluoric acid 40% T: Formaldehyde 37%
EN ISO 374-5	MICRO-ORGANISMS
	Protection against bacteria and fungi

## PRODUCT DETAILS

Interior finish	Flocked
Exterior finish	Embossed texture
Material	Polychloroprene and natural latex
Cuff characteristic	Straight cuff
Colours	Black
Length (cm)	31-32
Thickness (mm)	0.55
European sizes	7 8 9 10
Surface resistance according to EN1149-1 (Value in palm area at 25% relative humidity)	2.2E+11 Ω
Vertical resistance according to EN1149-2 (Value in palm area at 25% relative humidity)	1.5E+11 Ω

## LOGISTIC DETAILS

Packaging	1 pair/bag 10 pairs/bag 100 pairs/carton
-----------	--

## LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/08/18/1647
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France