


## Features

- Specifically designed for fast, clean cutting through aluminium and other non-ferrous metals.
- Manufactured from premium High-Speed Steel (HSS), this blade delivers outstanding strength, heat resistance, and extended cutting life in demanding metalworking applications.
- Featuring milled, side-set teeth and precision-engineered oval gullets, it ensures smooth and efficient cutting performance. Ideal for use on aluminium sheet (3–15mm), pipes, and profiles up to 25mm in diameter.

## Jigsaw Blade –Metal & Alu T127D –Special Cut

RS Stock No.: 0757842



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

## Product Description

### RS PRO Jigsaw Blade

0757842 Special for Metal/Alu Jigsaw Blade is specifically designed for fast, clean cutting through aluminium and other non-ferrous metals. Manufactured from premium High-Speed Steel (HSS), this blade delivers outstanding strength, heat resistance, and extended cutting life in demanding metalworking applications. Featuring milled, side-set teeth and precision-engineered oval gullets, it ensures smooth and efficient cutting performance. Ideal for use on aluminium sheet (3–15mm), pipes, and profiles up to 25mm in diameter.

- *Wavy Set Teeth for fine, straight cutting*
- *Suitable for use on Mild Steel, Sheet Steel, High Grade Steel & Steel Pipes*
- *Bayonet (T-Shank) fitting system compatible with all popular brands of bayonet fitting machines*
- *Supplied in 5pc Packs*

## General Specifications

<b>Tooth Design</b>	Side Set, Milled
<b>Type</b>	Jigsaw Blade
<b>Teeth Spacing</b>	3.0mm
<b>Cut Depth</b>	2.5–6mm
<b>Cut Type</b>	Special Cutting
<b>Material</b>	High Speed Steel
<b>Fitting</b>	Bayonet (T-Shank)
<b>Length</b>	100mm

Stock No.	Cut Type	Teeth Spacing	Length	Tooth Design
XXX-XXXX 0757836	Standard Cutting	1.1–1.5mm	77mm	Wavy Set, Milled
XXX-XXXX 0757837	Standard Cutting	1.9–2.3mm	77mm	Wavy Set, Milled
XXX-XXXX 0757838	Standard Cutting	0.7mm	77mm	Wavy Set, Milled
XXX-XXXX 0757839	Standard Cutting	1.2mm	132mm	Wavy Set, Milled
XXX-XXXX 0757840	Standard Cutting	2.0mm	132mm	Wavy Set, Milled
XXX-XXXX 0757842	Special Cutting	3.0mm	100mm	Side Set, Milled

## Approvals

<b>Declarations</b>	REACH DoC
---------------------	-----------

## Similar Products

Stock No.	Brand	Product Name	Cut Type	Teeth Spacing	Length	Tooth Design
XXX-XXXX 0757836	RS PRO	Jigsaw Blade	Standard Cutting	1.1-1.5mm	77mm	Wavy Set, Milled
XXX-XXXX 0757837	RS PRO	Jigsaw Blade	Standard Cutting	1.9-2.3mm	77mm	Wavy Set, Milled
XXX-XXXX 0757838	RS PRO	Jigsaw Blade	Standard Cutting	0.7mm	77mm	Wavy Set, Milled
XXX-XXXX 0757839	RS PRO	Jigsaw Blade	Standard Cutting	1.2mm	132mm	Wavy Set, Milled
XXX-XXXX 0757840	RS PRO	Jigsaw Blade	Standard Cutting	2.0mm	132mm	Wavy Set, Milled
XXX-XXXX 0757842	RS PRO	Jigsaw Blade	Special Cutting	3.0mm	100mm	Side Set, Milled

Connection Diagrams / Assembly Diagrams / Illustrations / Accessories