

Features

- ESD – Designed to safely discharge static electricity and protect electronic components from electrostatic discharge events.
- Wheeled
- Height Adjustable
- Back Adjustable
- Seat Adjustable
- Available in different sizes

RS PRO ESD Polyurethane Chair

RS Stock No.: 0665638



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Antistatic Polyurethane Chair is a professional solution designed for environments where effective electrostatic discharge (ESD) control is essential. It combines comfort, durability, and safety, meeting the demands of intensively used workstations.

Product Features:

- ✓ **Soft, anti-slip seat material** – ensures user comfort and effective ESD protection
- ✓ **Adjustable seat and backrest height** – allows personalized adjustment to meet individual user needs
- ✓ **Chrome-plated five-star base** – offers excellent stability and resistance to intensive use
- ✓ **Conductive castors** – rubber-coated to protect floor surfaces and support ESD protection
- ✓ **Easy-to-clean surface** – resistant to dirt and does not absorb contaminants
- ✓ **Carefully designed seat and backrest shape** – provides natural spinal support and enhances comfort during prolonged sitting

An ideal solution for production and service environments where reliable protection against electrostatic discharge is required. Perfectly suited for industries such as electronics, automotive, general manufacturing, medical, pharmaceutical, and military sectors.

General Specifications

TOTAL HEIGHT (mm)	780-985
TOTAL WIDTH (mm)	640
WEIGHT (kg)	10,2
MAX LOAD CAPACITY (kg)	120 (up to 200 kg with a special gas lift)
HEIGHT ADJUSTMENT RANGE (mm)	440-570mm
SEAT DIMENSIONS (mm)	465 x 440
BACKREST DIMENSIONS (mm)	130 x 420
ESD	YES
COLOUR	BLACK
MATERIAL	POLYURETHANE
BASE MATERIAL	CHROME-PLATED STEEL
CASTORS	CONDUCTIVE, RUBBER-COATED TO PREVENT SCRATCHING
RESISTANCE GROUNDING (Ωm)	10 ⁶ – 10 ⁸

Approvals

Chair compliance with standards	PN-EN IEC 61340-5-1:2025-02, PN-EN 1335-1:2004, PN-EN 1335-2:2009, PN-EN 1335-3:2009, PN-EN 1022:2007
---------------------------------	---

Similar Products

Stock No.	Brand	Product Name
0665639	RS PRO	ESD PU chair, seat height adjustment 525-710mm
0665640	RS PRO	ESD PU chair, seat height adjustment 580-830mm
0665652	RS PRO	ESD PU Comfort chair, seat height adjustment 430-560mm
0665653	RS PRO	ESD PU Comfort chair, seat height adjustment 510-700mm
0665654	RS PRO	ESD PU Comfort chair, seat height adjustment 550-800mm

Accessories

Stock No.	Brand	Product Name
0665661	RS PRO	ESD castor, grey rubber tyre, diameter 50mm (**brake option available on request**)
0665662	RS PRO	ESD metal castor, diameter 50mm
0665664	RS PRO	ESD glides
0665665	RS PRO	ESD footrest
0665666	RS PRO	ESD PU armrests
0665668	RS PRO	ESD armrests, black steel + antistatic PU cover
0665670	RS PRO	ESD armrests with height adjustment, black steel + antistatic PU covers