



Pushing Performance
Since 1945

T1 IP20 -M8 T1 SPE 1x2xAWG24/7 Rail 2.0m



Image is for illustration purposes only. Please refer to product description.

Part number	33 28 020 8004 020
Specification	T1 IP20 -M8 T1 SPE 1x2xAWG24/7 Rail 2.0m
HARTING eCatalogue	https://b2b.harting.com/33280208004020

Identification

Category	System cabling
Series	HARTING T1 Industrial
Element	Cable assemblies
Specification	Pre-assembled on both sides
Connector 1	HARTING T1 Industrial Overmoulded
Connector 2	HARTING M8 T1 Industrial Overmoulded
Type of cable	Copper cable (round)
Description of the cable	Flame retardant Oil resistant Halogen-free

Version

Cable length	2 m
Number of cores	2
Core structure	1x 2x AWG 24/7
Number of contacts	2

Technical characteristics

Rated current	4 A
Rated voltage	60 V DC
Transmission characteristics	600 MHz Bandwidth



Pushing Performance
Since 1945

Technical characteristics

Data rate	10 Mbit/s
	100 Mbit/s
	1 Gbit/s
Limiting temperature	-40 ... +80 °C unmoved
	-25 ... +80 °C moved
Mating cycles	≥100
Degree of protection acc. to IEC 60529	IP20
Test voltage $U_{r.m.s.}$	1 kV (contact-contact)
	2.25 kV (contact-ground)

Material properties

Material (cable)	XLPE
Colour (cable)	Black
RoHS	compliant
ELV status	compliant
China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R15 (HL 1-3)
	R16 (HL 1-3)

Specifications and approvals

Specifications	IEC 63171-6
	IEEE 802.3bu (remote power supply over PoDL = Power over Data Line)
	IEEE 802.3cg (10BASE-T1)
	IEEE 802.3bw (100BASE-T1)
	IEEE 802.3bp (1000BASE-T1)
	EN 45545-2 Hazard Level HL1-HL3
	EN 50305 clause 9.1.2
	IEC 60332-1-2
	IEC 60332-3-25
	IEC 60332-3-22 Flame retardancy
	EN 60811-404 Oil resistance

Commercial data

Packaging size	1
----------------	---



Pushing Performance
Since 1945

Commercial data

Country of origin	Latvia
European customs tariff number	85444290
GTIN	5713140564633
eCl@ss	27060307 Bus cable