

C-FCI 6/M8 - Fork-type cable lug



3240045

<https://www.phoenixcontact.com/gb/products/3240045>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Fork-type cable lug, yellow, 4 - 6 mm², M8

Your advantages

- The fork-type cable lugs without plastic sleeve feature a hard-soldered neck. In conjunction with the CRIMPFOX-RC ... and CRIMPFOX-RCI ... pliers they can be used to achieve maximum conductor pull-out forces
- The insulated versions are halogen-free and feature "EASY ENTRY" technology

Commercial data

Item number	3240045
Packing unit	25 pc
Minimum order quantity	100 pc
Sales key	BH3441
Product key	BH3441
Catalog page	Page 495 (C-3-2019)
GTIN	4046356452625
Weight per piece (including packing)	2.4 g
Weight per piece (excluding packing)	2.327 g
Customs tariff number	85369010
Country of origin	CN

C-FCI 6/M8 - Fork-type cable lug

3240045

<https://www.phoenixcontact.com/gb/products/3240045>




Technical data

Product properties

Product type	Connector
Product property	With “Easy Entry” system
	Brazed
	PA-insulated

Dimensions

Dimensional drawing	
Width	13.5 mm
Sleeve length	32.6 mm
Length of the insulating material sleeve	14 mm
Maximum stripping length	9 mm
Distance from the center to the insulating material sleeve	11.5 mm
Min. material thickness	1 mm
Inner dimensions of the insulating collar	6.6 mm

Internal dimensions

Internal diameter	8.5 mm
-------------------	--------

Material specifications

Color	yellow (RAL 1018)
Material	Copper
Flammability rating according to UL 94	V2
Coating	tin-plated
Insulating material	PA
Components	halogen-free

Mechanical properties

Technical data

Sleeve length	32.6 mm
---------------	---------

C-FCI 6/M8 - Fork-type cable lug


3240045

<https://www.phoenixcontact.com/gb/products/3240045>



Drawings

Dimensional drawing



C-FCI 6/M8 - Fork-type cable lug



3240045

<https://www.phoenixcontact.com/gb/products/3240045>

Classifications

ECLASS

ECLASS-13.0	27400204
-------------	----------

ETIM

ETIM 9.0	EC001052
----------	----------

UNSPSC

UNSPSC 21.0	27121700
-------------	----------

C-FCI 6/M8 - Fork-type cable lug

3240045

<https://www.phoenixcontact.com/gb/products/3240045>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk