

## 3 ft. (1 m) Thunderbolt 3 Cable with 100W Power Delivery - 40Gbps

Product ID: TBLT3MM1MA



This Thunderbolt 3 cable lets you deliver video and data to your Thunderbolt and USB-C devices from a Thunderbolt 3 laptop.

### Unbelievable Data Transfer Speeds

Transfer a 4K movie in seconds and complete backups in minutes with this Thunderbolt 3 USB-C cable, supporting data transfer rates of 40Gbps when connected to a Thunderbolt 3 device. You can transfer photo and video files at four times the speed of a USB 3.1 (10Gbps) cable.

### Enjoy Full 5K Video or Dual 4K Video

The cable supports up to 5K 60Hz video for astonishing resolution, contrast, and color depth with a Thunderbolt monitor. Or, use the cable with a Thunderbolt 3 dock to drive dual 4K displays.

## **Experience Versatile Power Delivery**

The Thunderbolt 3 Type-C cable delivers up to 100W of power for charging a Thunderbolt 3 laptop. It lets you keep your Thunderbolt 3 devices powered without needing an additional power supply.

## **Enable Thunderbolt Networking**

The cable gives you an easy way to bridge multiple Thunderbolt 3 USB-C enabled laptops for peer-to-peer 10GbE networking. It's perfect for setting up small work groups and sharing peripherals such as printers and storage. You can also connect two Thunderbolt 3 laptops together, for easy PC migrations.

TBLT3MM1MA is Thunderbolt Certified for guaranteed reliability and is backed by a StarTech.com 2-year warranty.

### Certifications, Reports and Compatibility



### Applications

- Connect your Thunderbolt 3 devices
- Power and charge Thunderbolt 3 devices
- Charge USB 2.0 mobile devices
- Set up peer-to-peer networking for multiple Thunderbolt 3 laptops

### Features

- Experience unbelievable data transfer rates of up to 40Gbps when connected to Thunderbolt 3 devices
- Connect to a full 5K or two 4K Thunderbolt or Ultra HD monitors
- Charge and power your Thunderbolt 3 devices with 100W of power delivery
- Provide superior connections with a Thunderbolt certified Thunderbolt 3 cable
- Easily network Thunderbolt 3 laptops and share printers and storage

<b>Hardware</b>	Warranty	2 Years
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Cable Shield Type	Aluminum-Mylar Foil with Braid
	Connector Plating	Nickel
<b>Performance</b>	Type and Rate	Thunderbolt 3 - 40 Gbit/s USB 2.0 - 480 Mbit/s
<b>Connector(s)</b>	Connector A	1 - Thunderbolt™ 3 USB-C (24-pin) (40Gbps) Male
	Connector B	1 - Thunderbolt™ 3 USB-C (24-pin) (40Gbps) Male
<b>Special Notes / Requirements</b>	<b>Note</b>	This cable does not support native DisplayPort 1.2. You cannot connect your laptop directly to a DisplayPort monitor using this Thunderbolt 3 cable.  When using this cable with a USB-C device, the cable will support USB 2.0 data transfer speeds of up to 480 Mbit/s. This cable is not compatible with USB 3.0 (5Gbps) or USB 3.1 (10Gbps) USB Type-C devices such as external drives, docking stations, etc.
<b>Power</b>	Power Delivery	100W
<b>Physical Characteristics</b>	Cable Length	3.3 ft [1 m]
	Color	Black
	Product Length	3.3 ft [1 m]
	Weight of Product	1.7 oz [47 g]
<b>Packaging Information</b>	Package Height	0.6 in [16 mm]
	Package Length	8.9 in [22.5 cm]
	Package Width	4.9 in [12.5 cm]
	Shipping (Package) Weight	1.9 oz [55 g]
<b>What's in the Box</b>	Included in Package	1 - Thunderbolt 3 USB-C cable

Product appearance and specifications are subject to change without notice.