

GripX

Superior liquid resistance with an excellent wet, dry and oil grip.

GENERAL PURPOSE PROTECTION RANGE

NINJA[®] MAXIM

TECHNOLOGY FEATURES



GRIP SMART
Superior grip

Soft, flexible HPT™ (Hydropellant Technology) coating provides highest level of wet, oily, and dry grip

Encapsulated air pockets mitigate effects of light vibrations



FIT SMART
Form-fitting design

Lightweight liner fits like a second skin



BREATHE SMART
Breathability

Anti-wet liner wicks liquids from back of hand for 360° breathability

PERFORMANCE STANDARDS & PROPERTIES

Risk Scale	LOW → VERY HIGH					
Abrasion	0	1	2	3	4	-
Tear	0	1	2	3	4	-
Puncture	0	1	2	3	4	-

EN388:2016



3131X

ANSI



Cut

ANSI



Abrasion

ANSI



Puncture

COMPLIES TO

Australian Standard
AS/NZS 2161.3:2020



HYDROPELLENT TECHNOLOGY™
Superior Grip and Dexterity



SPECIFICATIONS

Product Code	NIGRPXHPTBK
Description	Maxim GripX
Length	25 cm
Coating	HPT™ (Hydropellent Technology)
Coating Variants	Palm Dipped
Coating Colour	Black
Liner	Nylon and Spandex Knitted Liner
Liner Colour	Black

Sizes and Band Colour

S/7	M/8	L/9
XL/10	2XL/11	3XL/12

APPLICATIONS / INDUSTRIES

- Construction & Infrastructure • Mining • Manufacturing
- Shipping and receiving • Warehousing, Materials Handling & Assembly • Horticulture

Ninja® is a premium quality safety glove brand that understands the hand protection needs of its customers and delivers through R&D expertise. Ninja® is a registered trademark of Midas Safety Innovations Limited.

www.ninjaloves.com/au

Australia 1300 783 606 | Singapore +65 6262 5252

GripX HV

Superior liquid resistance with an excellent wet, dry and oil grip, and hi-vis for compliance visibility.

GENERAL PURPOSE PROTECTION RANGE

NINJA[®]

MAXIM

TECHNOLOGY FEATURES



GRIP SMART
Superior grip

Soft, flexible HPT™ (Hydropellant Technology) coating provides highest level of wet, oily, and dry grip

Encapsulated air pockets mitigate effects of light vibrations



FIT SMART
Form-fitting design

Fine nylon / spandex liner feels like a second skin

Hi-vis finish for compliance visibility



BREATHE SMART
Breathability

Anti-wet liner wicks liquids from back of hand for 360° breathability

PERFORMANCE STANDARDS & PROPERTIES

Risk Scale	LOW → VERY HIGH					
Abrasion	0	1	2	3	4	-
Tear	0	1	2	3	4	-
Puncture	0	1	2	3	4	-

EN388:2016



3131X

ANSI



Cut

ANSI



Abrasion

ANSI



Puncture

COMPLIES TO

Australian Standard
AS/NZS 2161.3:2020



HYDROPELLENT TECHNOLOGY™
Superior Grip and Dexterity



SPECIFICATIONS

Product Code	NIGRPXHPTFY
Description	Maxim GripX HV
Length	25 cm
Coating	HPT™ (Hydropellent Technology)
Coating Variants	Palm/Knuckle/Fully Dipped
Coating Colour	Hi-Vis Yellow
Liner	Nylon and Spandex Knitted Liner
Liner Colour	Hi-Vis Yellow

Sizes and Band Colour

S/7	M/8	L/9
XL/10	2XL/11	3XL/12

APPLICATIONS / INDUSTRIES

- Construction & Infrastructure • Mining • Manufacturing
- Shipping & Receiving • Horticulture
- Warehousing, Materials Handling & Assembly

Ninja® is a premium quality safety glove brand that understands the hand protection needs of its customers and delivers through R&D expertise. Ninja® is a registered trademark of Midas Safety Innovations Limited.

www.ninjaloves.com/au

Australia 1300 783 606 | Singapore +65 6262 5252