


Model No.DFT087F CORDLESS SCREWDRIVER



Model No.DFT087F CORDLESS SCREWDRIVER

Item No.	Parts No.	Description	Interchangability	Q'ty	New/Old	Note1	Note2
001	345344-4	PLATE H		1			
002	183W31-3	HOUSING SET		1	*		
C10	263005-3	RUBBER PIN 6		2	*		
C20	931002-4	HEX. NUT M3		9	*		
002		INC. 53			*		
002-1	1830L9-2	HOUSING SET	S	1			
C10	263005-3	RUBBER PIN 6		2			
C20	931002-4	HEX. NUT M3		9			
002-1		INC. 53					
003	620622-6	LED CIRCUIT		1			
004	457484-7	LENS		1			
005	412712-7	CHANGE PLATE		1			
006	233025-1	COMPRESSION SPRING 2		1			
007A	140U90-8	SWITCH LEVER COMPLETE		1	*		
007-1 A	141N44-6	SWITCH LEVER COMPLETE	<	1	*		
007-1 B	141N44-6	SWITCH LEVER COMPLETE		1	*		
007-2	141Y37-9	SWITCH LEVER COMPLETE	S	1			
008	620D61-4	SENSOR CIRCUIT		1			
009	620J83-0	USB CIRCUIT		1			
010	144709-5	USB COVER COMPLETE		1			
011	620J82-2	LED CIRCUIT		1			
012	457469-3	F/R CHANGE LEVER		1			
013	651082-1	SWITCH C3JW-1B-S		1			
014	620621-8	BUZZER CIRCUIT		1			
015	233930-2	RING SPRING 9		1			
016	267070-4	FLAT WASHER 10		1			
017	232374-3	COMPRESSION SPRING 10A		1			
018	161607-8	BIT SLEEVE		1			
019	457530-6	LOCK NUT M28 BLACK		1			
020	213836-0	O-RING 22		1			
021	216015-9	STEEL BALL 2.4		2			
022	122C82-1	CLUTCH ASSEMBLY 8MR		1	*		
022		INC. 23-36			*		
022-1	122H22-9	Clutch assembly 8MR	<	1			
022-1		INC. 23-36					
023	961026-6	RETAINING RING S-10		1			
024	210076-1	BALL BEARING 6800LLB		1			
025A	232375-1	COMPRESSION SPRING 10B		1	*		
025-1 A	232656-3	COMPRESSION SPRING 11	O	1			
025-1 B	232656-3	COMPRESSION SPRING 11		1			
026	267047-9	FLAT WASHER 10		1			
027	324834-0	LOCK NUT M12		1			
028	158408-3	ADJUST RING COMPLETE		1			
029	267276-4	FLAT WASHER 18		1			
030	327A31-3	SPINDLE MR		1			

031	216018-3	STEEL BALL 5.0		3			
032	233384-3	COMPRESSION SPRING 19E		1			
033	223146-7	CAM D		1	*		
033-1	223202-3	Cam G	S	1			
034	216024-8	STEEL BALL 4		3			
035	223187-3	CAM F		1	*		
035-1	223203-1	Cam H	S	1	*		
035-2	223206-5	Cam I	O	1			
036	216024-8	STEEL BALL 4		7			
037	136814-2	GEAR ASSEMBLY		1	*		
037		INC. 38-46			*		
037-1	137139-7	GEAR ASSEMBLY	<	1	*		
037-1		INC. 38-46			*		
037-2	1915J8-6	Gear assembly P	O	1			
037-2		INC. 38-46					
038	153443-6	CARRIER COMPLETE A		1	*		
038-1	1410C7-9	Carrier complete A	<	1			
039	211375-4	BALL BEARING 6805LLB		1			
040	413J94-0	GEAR CASE		1	*		
040-1	4130Y3-4	GEAR CASE	S	1			
041	227048-9	INTERNAL GEAR 47		1			
042	227050-2	SPUR GEAR 13		3			
043	153445-2	SPUR GEAR 20 COMPLETE A		1			
044	227049-7	SPUR GEAR 18		3			
045	267774-8	LOCK WASHER		1			
046	418003-4	MOTOR BRACKET		1			
047	266490-9	TAPPING SCREW PT 2X6		3			
048	652069-6	FLAT HEAD SCREW M3X6		3			
049A	620J80-6	CONTROLLER		1			
049B	620N36-3	Controller		1			
050	629B33-4	STATOR		1			
051	619442-3	ROTOR		1			
052	643874-2	TERMINAL		1			
053	183W31-3	HOUSING SET		1	*		
C10	263005-3	RUBBER PIN 6		2	*		
C20	931002-4	HEX. NUT M3		9	*		
053		INC. 2			*		
053-1	1830L9-2	HOUSING SET	S	1			
C10	263005-3	RUBBER PIN 6		2			
C20	931002-4	HEX. NUT M3		9			
053-1		INC. 2					
054	251581-9	PAN HEAD SCREW M3X20		8			
055	412358-9	COVER		1			
056	911013-5	PAN HEAD SCREW M3X10		1			
057	858T32-9	DFT087F SERIAL NO. LABEL		1			
058	858T27-2	DFT087F NAME PLATE		1			

Please state Parts No. when your order.

Print Date 06/09/2025