


Engraving material - GPE 17,5X12 WH - 0806916

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)

Engraving material, Sheet, white, unlabeled, can be labeled with: Engraving, Plotter, Mounting type: Adhesive, Lettering field: 17.5 x 12 mm




The figure shows the version GPE 20x8 WH

Why buy this product

- Can be labeled easily using the CMS-P1-PLOTTER
- Can be engraved using the P1 ENGRAVING UNIT
- The adhesive foil used ensures good adhesive properties, even on uneven surfaces
- Labeling service: Phoenix Contact can custom-label all GPE ... markers according to your requirements
- Two-layer material
- The label sheet consists of prefabricated, individual self-adhesive labels



Key commercial data

| | |
|--------------------------------------|---|
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| GTIN |  4 017918 145071 |
| Weight per Piece (excluding packing) | 19.24 g |
| Custom tariff number | 39203000 |
| Country of origin | Germany |
| Note | Made to Order (non-returnable) |

Technical data

Dimensions

| | |
|-----------|---------|
| Height | 12 mm |
| Width (a) | 17.5 mm |

Ambient conditions

| | |
|---------------------------------|---|
| Ambient temperature (operation) | -20 °C ... 85 °C |
| Recommended storage conditions | 20°C/50% relative humidity. Storage in the original packaging is recommended. |

Engraving material - GPE 17,5X12 WH - 0806916

Technical data

General

| | |
|-------------------------------------|--------------------------------|
| Note | Can be labeled with CMS |
| Color | white |
| Components | free from silicone and halogen |
| Material | TRANSPLY-ABS |
| Wipe resistance | DIN EN 61010-1 (VDE 0411-1) |
| Number of individual labels | 75 |
| Number of individual labels per row | 5 |
| Adhesive | Acrylic |
| Printability | Engraving |
| | Plotter |
| Device | 5144615 CMS-P1-PLOTTER |
| | 5145546 P1 ENGRAVING UNIT |
| Adhesive strength | 50 µm |
| Marking mounting type | Adhesive |

Classifications

eCl@ss

| | |
|------------|----------|
| eCl@ss 4.0 | 24190218 |
| eCl@ss 4.1 | 24190218 |
| eCl@ss 5.0 | 27141137 |
| eCl@ss 5.1 | 27141137 |
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |

ETIM

| | |
|----------|----------|
| ETIM 2.0 | EC000761 |
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

UNSPSC

| | |
|---------------|----------|
| UNSPSC 6.01 | 30211811 |
| UNSPSC 7.0901 | 39121410 |
| UNSPSC 11 | 39121410 |
| UNSPSC 12.01 | 39121410 |
| UNSPSC 13.2 | 39121410 |

Drawings

Engraving material - GPE 17,5X12 WH - 0806916

Dimensioned drawing

