

S-Video or Composite to HDMI Converter with Audio - 720p - NTSC and PAL

Product ID: VID2HDCON2



This S-Video or composite to HDMI converter with audio lets you connect an S-Video or analog composite device, along with supporting RCA L/R audio, to your HDMI monitor or television.

Hassle-Free Setup and Easy to Use

Equipped with an on-screen display (OSD) menu and convenient selector switches for easy configuration, this compact S-Video or composite to HDMI video converter installs quickly and easily, for a true plug-and-play experience.

Save on Upgrade Costs

This HDMI upscaler is able to function with both NTSC and PAL systems, and offers support for output resolutions up to 720p to seamlessly integrate with almost any display.

By using this analog to HDMI converter you'll be able to continue using your legacy equipment (video camera, DVD player, etc.) with your HDMI display or monitor, ultimately saving the costs of upgrading your equipment. It's ideal for boardroom settings, medical imaging and watching old home videos on your HD display or television.

Support for Audio

This AV (audio video) converter box features an integrated RCA L/R audio connection that combines the audio and video inputs into a single HDMI output, avoiding the hassle of running a separate audio cable to your destination display.

VID2HDCON2 is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Display video from a legacy gaming console, DVD player or VCR onto an HDMI display or TV
- Adapt VHS video in the classroom to newer HD televisions
- Convert legacy medical imaging equipment for display on computer monitors
- Display camcorder output on televisions or monitors equipped with HDMI input
- Monitor security cameras with analog composite signaling using HDMI monitors or televisions
- Use in boardrooms for connecting legacy video equipment to new projectors

Features

- Convert and upscale S-Video or analog composite input to HDMI video output
- Features on-screen display for simple setting selections
- Supports standard high-definition resolutions up to 720p
- Offers a pure hardware design, with no software installation required
- Video upscaler accepts NTSC or PAL input

Hardware	Warranty	2 Years
	Active or Passive Adapter	Active
	Audio	Yes
	AV Input	Audio RCA
		Composite
		S-Video
AV Output	HDMI	
Industry Standards	NTSC 3.58 and PAL	
Performance	Supported Resolutions	HDMI: 1280x720 (720p) / 60Hz
Connector(s)	Connector Type(s)	1 - Composite Video (1 x RCA) Female Input
		1 - HDMI (19 pin) Female Output
		1 - S-Video (4 pin, Mini-DIN) Female Input
		2 - RCA Female Input
Indicators	LED Indicators	1 - Power LED
		2 - Composite Video, S-Video LED
Power	Center Tip Polarity	Positive
	Input Voltage	100 - 240 AC
	Output Current	1
	Output Voltage	5 DC
	Plug Type	M
	Power Consumption (In Watts)	2.5
	Power Source	AC Adapter Included
Environmental	Humidity	10~85% RH
	Operating Temperature	0°C to 45°C (32°F to 113°F)
	Storage Temperature	-10°C to 80°C (14°F to 176°F)
Physical Characteristics	Color	Black
	Material	Plastic
	Product Height	23.000
	Product Length	6.1 in [15.4 cm]
	Product Width	75.000
	Weight of Product	251.000

Packaging Information	Package Height	60.000
	Package Length	250.000
	Package Width	200.000
	Shipping (Package) Weight	578.000
What's in the Box	Included in Package	1 - Composite/S-Video to HDMI Converter
		1 - Universal Power Adapter
		1 - Quick-Start Guide

Product appearance and specifications are subject to change without notice.