



| | | | |
|------------------------|---------------|-------------------------------|--------------|
| EAN: | 4013288101419 | Size: | 105x65x14 mm |
| Part number: | 05104620001 | Weight: | 17 g |
| Article number: | 848 HSS | Country of origin: | CN |
| | | Customs tariff number: | 82075060 |

- Twist bit for metal applications
- Hex shaft for very good power transfer
- HSS = high speed steel with split point
- Finely-tuned material elasticity for great durability
- Very good concentricity

High quality metal twist drill bits for precise drilling in metal. Made out of high speed steel (HSS). A finely-tuned material elasticity provides for a long service life. Very good concentricity. Tough viscous tempered bits ensure a particularly long service life. The hexagonal shaft ensures very good power transfer. Drive: 1/4" hexagon, suitable for holders as per DIN ISO 1173-D 6.3.

Web link

https://products.wera.de/en/bits_holders_adaptors_and_sets_bit_sets_bit_sets_for_special_applications_848_hss.html

Wera - 848 HSS
05104620001 - 4013288101419

Wera Werkzeuge GmbH
Korzter Straße 21-25
D-42349 Wuppertal
Tel: +49 (0)2 02 / 40 45-0
E-Mail: info@wera.de




Bit Sets for Special Applications

Twist drill bits for metal applications



Twist drill bits - for metal applications • ¼" drive suitable for holders as per DIN 3126-D 6.3 (ISO 1173) • Hexagon shaft for very high torque transfer • HSS = high speed steel with cone point • Finely adjusted material elasticity for long service life • Excellent concentricity • Tough-absorbing tempered bits for particularly long service life

Further versions in this product family:

| |  mm |  mm |  mm |
|--------------------|---|---|---|
| 05104610001 | 3.0 | 16.00 | 38.0 |
| 05104611001 | 3.1 | 18.00 | 40.0 |
| 05104612001 | 3.3 | 18.00 | 40.0 |
| 05104613001 | 4.0 | 20.00 | 44.0 |
| 05104614001 | 4.1 | 20.00 | 44.0 |
| 05104615001 | 4.2 | 20.00 | 45.0 |
| 05104616001 | 5.0 | 26.00 | 50.0 |
| 05104617001 | 5.1 | 26.00 | 50.0 |
| 05104618001 | 6.0 | 26.00 | 50.0 |
| 05104619001 | 6.8 | 30.00 | 50.0 |
| 05104620001 | 8.0 | 32.00 | 51.0 |
| 05104621001 | 8.5 | 33.00 | 53.0 |
| 05104622001 | 10.0 | 38.00 | 54.0 |

Web link

https://products.wera.de/en/bits_holders_adaptors_and_sets_bit_sets_bit_sets_for_special_applications_848_hss.html

Wera - 848 HSS
 05104620001 - 4013288101419

Wera Werkzeuge GmbH
 Korzter Straße 21-25
 D-42349 Wuppertal
 Tel: +49 (0)2 02 / 40 45-0
 E-Mail: info@wera.de