

General Information

| | |
|------------------------|--|
| Extended Product Type: | 263BS6W |
| Product ID: | 2CMA167340R1000 |
| EAN: | 7392696673402 |
| Catalog Description: | Surface inlet, 6h, 63A, IP67, 2P+E |
| Long Description: | Surface Inlet, earthing sleeve position 6h, rated current 63A, IP67 watertight, 2-poles+earth, frequency 50-60 Hz, color code Blue |

Categories

Products » Low Voltage Products and Systems » Industrial Plugs and Sockets » Plugs & Sockets » Surface Inlets

Ordering

| | |
|-------------------------|---------------------|
| EAN: | 7392696673402 |
| Minimum Order Quantity: | 1 piece |
| Country of Origin: | Czech Republic (CZ) |

Dimensions

| | |
|---------------------|--------|
| Product Net Width: | 118 mm |
| Product Net Height: | 249 mm |
| Product Net Length: | 138 mm |
| Product Net Depth: | 249 mm |
| Product Net Weight: | 1.2 kg |

Container Information

| | |
|-------------------------------|---------------|
| Package Level 1 Width: | 124 mm |
| Package Level 1 Length: | 337 mm |
| Package Level 1 Height: | 153 mm |
| Package Level 1 Gross Weight: | 1.2 kg |
| Package Level 1 EAN: | 7392696673402 |
| Package Level 1 Units: | 1 piece |

Environmental

| | |
|--------------|--|
| RoHS Status: | Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2006-03-01 |
|--------------|--|

Certificates and Declarations (Document Number)

| | |
|---------------------------------|-----------------|
| Declaration of Conformity - CE: | 2CMC700005D0001 |
| Environmental Information: | 2CMC700001D0002 |
| RoHS Information: | 2CMC700057D0001 |

Additional Information

| | |
|----------------------------------|--------------------------------|
| Additional Information: | Cable entry \varnothing 32mm |
| Cable Cross-Section: | 6 ... 25 mm ² |
| Color: | Blue |
| Degree of Protection: | IP67 |
| Enclosure Material: | Thermoplastic polyester (PBT) |
| Frequency (f): | 60 Hz |
| Function: | Surface inlet |
| IIT Publishing Status: | Level 0 - Information enabled |
| Invoice Description: | Ind. P&S#263BS6W |
| Number of Poles: | 3 |
| Object Classification Code: | 2CMT005069 |
| Product Main Type: | BS |
| Product Name: | Industrial Surface Inlet |
| Protection Type: | Watertight |
| Rated Current (I _n): | 63 A |
| Rated Voltage (U _r): | 200 ... 250 V |
| RoHS Date: | L23 |
| Standards: | IEC 60309-1,-2 |
| Suitable For: | Surface Inlets |
| Suitable for Product Class: | Industrial Plugs and Sockets |

Classifications

E-nummer: 2417259

UNSPSC: 39120000

