

# FL19

## DUAL COLOR WIDE ANGLE FLOOD

330 LUMENS | 38M BEAM | 17H



The FL19 Headlamp combines our Wide Angle Flood Beam optic with a dual color feature that includes a white and red LED beam. As a result, the top button on the headlamp gives you the ability to cycle through light modes quickly. The Wide Angle Flood beam is a white LED light that illuminates large areas with an ultra-wide circular beam. Similarly, the top button on the headlamp enables the user to switch to red. The red LED light helps you preserve night vision. The headlamp comes with a reflective safety strap and an IPX4 weatherproof rating, making it perfect for any rugged environment you may find yourself.

With Coast's commitment to quality, the FL19 Headlamp is impact resistant, weather resistant and its LED is virtually unbreakable. The FL19 Headlamp is backed by Coast's lifetime warranty against defects in materials and workmanship. Tested and rated to ANSI/FL1 standards.

<b>BATTERY LOCATION</b>	Front
<b>BATTERY TYPE</b>	3 x AAA (Alkaline)
<b>BEAM DISTANCE (HIGH)</b>	124 ft / 38 m
<b>BEAM DISTANCE (LOW)</b>	49 ft / 15 m
<b>INCLUDED</b>	3 x AAA Batteries   Hardhat Clips   Reflective Safety Strap

<b>LIGHT OUTPUT (HIGH)</b>	330 Lumens
<b>LIGHT OUTPUT (LOW)</b>	45 Lumens
<b>RUNTIME (HIGH)</b>	3 h 15 min
<b>RUNTIME (LOW)</b>	17 h
<b>WEIGHT</b>	3 oz / 85 g



### DUAL-COLOR WHITE & RED BEAM

The right light for the moment. The Dual-Color White & Red Beam combines an all-white Utility Beam for general use with a red, anti-glare beam that prevents "night blinding" while also offering a tool for emergency signaling.



### HARDHAT COMPATIBLE

Rugged enough for the outside of the hardhat. COAST headlamps with Hardhat Compatible design include clips for attaching the light to the hat.



### HIGH/LOW

Control your light power with the push of a button. Cycle between High power and low power options.



### HINGED BEAM

Up, down, or straight ahead. All COAST headlamps feature a hinged, tilting head so that you can adjust the light's direction and see right where you're looking.



### REFLECTIVE STRAP

Stay visible in the dark. Some COAST headlamps feature a Reflective Strap to increase safety and ensure user visibility in low light.



### WATER RESISTANCE

Don't worry about the weather. COAST lights that have passed the IPX4-level water resistance test are splash-resistant and built with durable materials that stand up to nature.



### WIDE ANGLE FLOOD BEAM OPTIC

See the whole scene at once. The Wide Angle Flood Beam illuminates the broadest possible area with vivid, consistent light from edge to edge. At 6 feet / 1.8 meters distance, the beam shines a clear circle up to 11.5 feet / 3.5 meters in diameter.