


**Datasheet**  
**Hexagon Head Set Screw – DIN 933**  
**Grade 8.8 Plain Finish**  
 All Fully Threaded



| d1 | M6    | M8    | M10   | M12   | M16   | M20   |
|----|-------|-------|-------|-------|-------|-------|
| e  | 11.05 | 14.38 | 18.90 | 21.10 | 26.75 | 35.72 |
| k  | 4.0   | 5.3   | 6.4   | 7.5   | 10    | 13    |
| s  | 10    | 13    | 17    | 19    | 24    | 30    |

Please view our full range listing below

| RS Stock No | Size    | RS Stock No | Size      | RS Stock No | Size      | RS Stock No | Size      |
|-------------|---------|-------------|-----------|-------------|-----------|-------------|-----------|
| 1925537     | M6 x 12 | 1925555     | M8 x 100  | 1925573     | M12 x 35  | 1925591     | M16 x 100 |
| 1925538     | M6 x 16 | 1925556     | M8 x 120  | 1925574     | M12 x 40  | 1925592     | M16 x 120 |
| 1925539     | M6 x 20 | 1925557     | M10 x 20  | 1925575     | M12 x 45  | 1925593     | M20 x 30  |
| 1925540     | M6 x 25 | 1925558     | M10 x 25  | 1925576     | M12 x 50  | 1925594     | M20 x 40  |
| 1925541     | M6 x 30 | 1925559     | M10 x 30  | 1925577     | M12 x 60  | 1925595     | M20 x 50  |
| 1925542     | M6 x 40 | 1925560     | M10 x 40  | 1925578     | M12 x 70  | 1925596     | M20 x 55  |
| 1925543     | M6 x 50 | 1925561     | M10 x 50  | 1925579     | M12 x 75  | 1925597     | M20 x 60  |
| 1925544     | M6 x 60 | 1925562     | M10 x 60  | 1925580     | M12 x 80  | 1925598     | M20 x 70  |
| 1925545     | M8 x 16 | 1925563     | M10 x 65  | 1925581     | M12 x 90  | 1925599     | M20 x 80  |
| 1925546     | M8 x 20 | 1925564     | M10 x 70  | 1925582     | M12 x 100 | 1925600     | M20 x 90  |
| 1925547     | M8 x 25 | 1925565     | M10 x 75  | 1925583     | M16 x 35  | 1925601     | M20 x 100 |
| 1925548     | M8 x 30 | 1925566     | M10 x 80  | 1925584     | M16 x 40  | 1925602     | M20 x 120 |
| 1925549     | M8 x 40 | 1925567     | M10 x 90  | 1925585     | M16 x 45  |             |           |
| 1925550     | M8 x 50 | 1925568     | M10 x 100 | 1925586     | M16 x 50  |             |           |
| 1925551     | M8 x 60 | 1925569     | M10 x 120 | 1925587     | M16 x 60  |             |           |
| 1925552     | M8 x 70 | 1925570     | M12 x 20  | 1925588     | M16x 70   |             |           |
| 1925553     | M8 x 75 | 1925571     | M12 x 25  | 1925589     | M16 x 80  |             |           |
| 1925554     | M8 x 80 | 1925572     | M12 x 30  | 1925590     | M16 x 90  |             |           |