PressurePro Grease and Protein Remover RM 731

Removes even the toughest grease, protein, oil and soot contamination from floors, working areas, machines, etc. (particularly suitable for use in the food processing industry). Easy to use, with a gentle cleaning action. Washes off without residue.

pH value 13
in concentrate



NTA-free

Properties

- Effective high-pressure detergent
- Loosens heavy oil, grease and mineral-based soiling
- Suitable for cleaning stainless steel and ceramic surfaces
- Cleaning action in all temperature ranges
- Washes off without residue
- Tensides biodegradable in accordance with EEC 648/2004
- Quick oil and water separation in the oil separator (easily separable = asf)
- NTA-free

Application areas

Agriculture	Milk kitchens
Food and drink industry	Surface cleaning
Hotels, gastronomy, catering	Surface cleaning
Retail	Surface cleaning

Usage options

- High-pressure cleaners
- Spray units
- Manual

Technical data

Container sizes	Packaging unit	Part number
5 l	1 Piece(s)	6.295-402.0

We would be happy to advise you:

Application

High-pressure cleaners
- Set the dosage and temperature on the device
- Clean object.
- Allow to soak.
- Reaction time max. 1 min.
- Rinse with clear water.
- In food-processing applications, rinse thoroughly with drinking water.

Spray unit
- Combine the product with the appropriate dosage and fresh water.
- Wet object completely with the product.
- Allow to soak.
- Reaction time max. 1 min.
- Rinse with clear water.
- In food-processing applications, rinse thoroughly with drinking water.

Manual
- Combine the product with the appropriate dosage and fresh water.
- Clean object.
- Rinse with clear water.
- In food-processing applications, rinse thoroughly with drinking water.



Instructions for use

- In the food sector, rinse thoroughly with drinking water.
- Do not let the cleaning solution dry out.
- Do not spray onto hot surfaces.
- Avoid over-dosage.

Warnings and safety recommendations according to EC Directives

- Danger
- H290 May be corrosive to metals
- H314 Causes severe skin burns and eye damage
- P280 Wear protective gloves/protective clothing/eye protection/face protection.
- P305 + P351 + P338 IF IN EYES: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.
- P310 Immediately call a POISON CENTER/doctor.
- P303 + P361 + P353 IF ON SKIN (or hair): Take off immediately all contaminated clothing. Rinse skin with water [or shower].
- P405 Store locked up.
- P501a Dispose of contents/container in accordance with local/regional/national/international regulations.

Further information

- Material Safety Data Sheet (MSDS)

Dosage and yield

Contents	Cleaning method	Dosage	Soiling	Yield
1000 ml	High-pressure cleaners	1 – 6 %	strong	67 m²
1000 ml	Spray units	1 – 6 %	medium	1110 m²
1000 ml	Manual	1 – 6 %	medium	250 m²

We would be happy to advise you: