

## Features

- **Robust 304 Stainless Steel Construction** – Offers exceptional durability and corrosion resistance in harsh industrial environments.
- Ideal for indoor and outdoor industrial use in oil & gas, chemical, manufacturing, and refinery sectors - Environments prone to moisture, chemicals, or high temperatures.
- **Versatile Application** – Effectively isolates multiple energy sources like gate valves, handle valves, and machinery where traditional devices may not fit.
- **2-Meter SS Cable** - Stainless-steel cable attachment simplifies setup and ensures secure locking.
- **Tool-Free Twist Mechanism** – Allows manual tightening of the cable without the need for tools or keys.
- **Compact & Ergonomic Design** – Lightweight and easy to use in confined spaces.
- Designed to work with standard safety padlocks for effective lockout security.

## RS PRO Twister Metallic Multipurpose Cable Lockout with 2-meter SS Cable

RS Stock No.: 0694359



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

- *The Twister Metallic Multipurpose Cable Lockout is an innovative cable-based safety lockout solution designed for isolating a wide range of energy sources.*
- *Crafted from 304-grade stainless steel, this durable and corrosion-resistant device is ideal for harsh industrial environments where safety, strength, and longevity are essential.*
- *It is particularly useful for locking out multiple energy isolation points such as gate valves, handle valves, and other machinery where traditional devices may not fit.*
- *Includes a 2-meter-long stainless-steel cable integrated with the locking device*
- *Ergonomic twist mechanism enables manual tightening of the cable—no tools or keys required.*
- *Designed to be secured using a standard lockout padlock once the cable is tightened.*
- *Ideal for indoor and outdoor industrial use in oil & gas, chemical, manufacturing, and refinery sectors - Environments prone to moisture, chemicals, or high temperatures.*

## General Specifications

<b>Type</b>	Multipurpose Cable Lockout
<b>Material</b>	Stainless Steel 304
<b>Colour</b>	Natural Metallic Finish
<b>Padlock holes</b>	06
<b>Package</b>	PE-LD

## Mechanical Specifications

<b>Cable Length</b>	2 meters
<b>Cable Diameter</b>	4mm
<b>Locking Mechanism</b>	Manual twist-lock, padlock secured
<b>Compatibility</b>	Accepts unto 6 standard safety padlocks
<b>Weight</b>	310 Grams

## Operation Environment Specifications

<b>Withstand temperature</b>	-40 °C to +120 °C
------------------------------	-------------------