


BW 5945/2024
Tools organised in soft trays made of EVA (Ethylene Vinyl Acetate). Assortment compatible with Beta C45PRO workshop furniture.

	Art.
	
059456302	BW 5945/2024

- n. 21 **BW 42:** Combination wrenches □ □
6-7-8-9-10-11-12-13-14-15-16-17-18-19-20-21-22-24-27-30-32 mm
- n. 9 **BW 96BPC/SC9:** Set of 9 ball head offset hexagon key wrenches □ □
1,5-2-2,5-3-4-5-6-8-10 mm
- n. 1 **BW 1166BM:** Extra-long needle knurled nose pliers □ □ 160 mm
- n. 1 **BW 1150BM:** Heavy-duty combination pliers □ □ 180 mm
- n. 1 **BW 1082BM:** Diagonal cutting nippers □ □ 160 mm
- n. 22 **BW 1256/C21-1:** Micro screwdriver with 21 interchangeable inserts
4 mm and handle □ 4 mm
- n. 1 **BW 1052:** Adjustable self-locking pliers, concave jaws 240 mm
- n. 1 **BW 1048:** Slip joint pliers, boxed joints 250 mm
- n. 1 **BW 1253:** Mains testing screwdriver □ □ 3,5x100 mm
- n. 2 **BW 34:** Flat chisels 150-175 mm
- n. 1 **BW 1719BMA8/Q:** Second-cut square files, with handles B 200 mm
- n. 1 **BW 1719BMA8/T:** Second-cut triangular files, with handles ▲ 200 mm
- n. 1 **BW 1719BMA8/P:** Second-cut flat files, with handles ▮ 200 mm
- n. 1 **BW 1719BM/RR:** Round rasp, plastic handle S 200 mm
- n. 1 **BW 1719BMA8/M:** Second-cut half-round files, with handles 200 mm
- n. 1 **BW 1370:** Engineer's hammers □ 300 g
- n. 1 **BW 1390:** Soft face hammer, plastic faces Ø 35 mm
- n. 9 **BW 900L:** Hexagon hand sockets, long series, 1/4" □ □ □
5-6-7-8-9-10-11-12-13 mm
- n. 5 **BW 900ME:** Socket drivers for hexagon screws, 1/4" □ □ □ 3-4-5-6-7 mm
- n. 4 **BW 900LP:** Socket drivers for slotted head screws, 1/4" □ □ □
0,8x4-1x5,5-1,2x6,5-1,2x8 mm
- n. 3 **BW 900PH:** Socket drivers for cross head Philips® screws, 1/4" □ □ □
PH1-PH2-PH3
- n. 6 **BW 900TX:** Socket drivers for Torx® head screws, 1/4" □ □ □
T10-T15-T20-T25-T27-T30
- n. 1 **BW 900/20:** Extension cords - 1/4" 50 mm
- n. 1 **BW 900/20L:** Extension cords - 1/4" 100 mm
- n. 1 **BW 900/25:** Universal joint - 1/4"
- n. 1 **BW 900/30:** 1/4" drive spinner handle 150 mm
- n. 1 **BW 895/1:** Socket holders for items BW 861, BW 862, BW 866 □
1/4" - E 1/4"
- n. 1 **BW 895/3:** Socket holders for items BW 861, BW 862, BW 866 □
1/4" - E 3/8"
- n. 1 **BW 895/6:** Socket holders for items BW 861, BW 862, BW 866 □
5/16" - E 1/2"
- n. 13 **BW 900:** Hexagon hand sockets, 1/4" □ □ □
4-4,5-5-5,5-6-7-8-9-10-11-12-13-14 mm
- n. 2 **BW 956C:** Spark plug sockets, 1/2" female square drive □ □ 16-21 mm
- n. 2 **BW 956C:** Spark plug sockets, 1/2" female square drive □ □ 16-21 mm



Scan the QR Code to access the web tab
Specs, media and documentation in one click.

