



Product Data Sheet

Metric Five Layer Pex Barrier Pipe



John Guest



The John Guest Metric five Layer Pex Barrier Pipe is manufactured to BS 7291 Parts 1 and 3 Class 'S' and is Kitemarked for Hot & Cold water and Central Heating.

Working Pressures and Temperatures

Water 12½ Bar at 20°C 4 Bar at 82°C 3 Bar AT 92°C

Minimum Temperature 1°C

All Dimensions in mm

THE COPYRIGHT IN THIS DRAWING AND THE PRODUCTS REFERRED THEREON BELONG TO JOHN GUEST INTERNATIONAL LIMITED AND THIS DRAWING NOR THE INFORMATION CONTAINED HEREIN SHALL BE PRODUCED IN ANY FORM OR USED FOR ANY PURPOSE WITHOUT WRITTEN CONSENT © 2007

The company has a policy of continuous research and development and reserves the right to amend without notice the specification and design of all products illustrated. For details of terms and conditions and any other technical enquiries, please contact our Customer Services Department.

ISSUE 8 GA 09-09-08

DS-BPEX

(sht 1 of 3 shts)

Product Data Sheet

Metric Five Layer Pex Barrier Pipe



John Guest

Product No.	Description (Nominal Diameter x Length)	Pipe O/D	Pipe I/D	Ovality			
10BPEX-25C	10mm x 25M Coil of SpeedpexPipe	9.9 - 10.1	6.6 - 6.8	0.5 Max			
10BPEX-50C	10mm x 50M Coil of Speedpex Pipe						
10BPEX-100C	10mm x 100M Coil of Speedpex Pipe						
12BPEX-20X3L	12mm x 3M Bundle of 20 Speedpex Pipe	11.9 - 12.1	8.6 - 8.8	0.5 Max			
12BPEX-50C	12mm x 50M Coil of Speedpex Pipe						
12BPEX-100C	12mm x 100M Coil of SpeedpexPipe						
15BPEX-10X2L	15mm x 2M Bundle of 10 Speedpex Pipe	14.9 - 15.1	11.45 - 11.65	1.0 Max			
15BPEX-10X3L	15mm x 3M Bundle of 10 Speedpex Pipe						
15BPEX-20x2L	15mm x 2M Bundle of 20 Speedpex Pipe						
15BPEX -20x3L	15mm x 3M Bundle of 20 Speedpex Pipe						
15BPEX-20x5L	15mm x 5M Bundle of 20 Speedpex Pipe						
15BPEX-20x6L	15mm x 6M Bundle of 20 Speedpex Pipe						
15BPEX-25C	15mm x 25M Coil of SpeedpexPipe						
15BPEX-30C	15mm x 30M Coil of Speedpex Pipe						
15BPEX-50C	15mm x 50M Coil of Speedpex Pipe						
15BPEX-100C	15mm x 100M Coil of Speedpex Pipe						
15BPEX-120C	15mm x 120M Coil of Speedpex Pipe						
15BPEX-150C	15mm X 150M Coil of Speedpex Pipe						
22BPEX-10X2L	22mm x 2M Bundle of 10 Speedpex Pipe				21.9 - 22.1	17.6 - 17.8	1.0 Max
22BPEX-10X3L	22mm x 3M Bundle of 10 Speedpex Pipe						
22BPEX-20x2L	22mm x 2M Bundle of 20 Speedpex Pipe						
22BPEX -20x3L	22mm x 3M Bundle of 20 Speedpex Pipe						
22BPEX-20x5L	22mm x 5M Bundle of 20 Speedpex Pipe						
22BPEX-20x6L	22mm x 6M Bundle of 20 Speedpex Pipe						
22BPEX-25C	22mm x 25M Coil of SpeedpexPipe						
22BPEX-50C	22mm x 50M Coil of Speedpex Pipe						
28BPEX -10x3L	28mm x 3M Bundle of 10 Speedpex Pipe	27.9 - 28.1	22.4 - 22.6	1.0 Max			
28BPEX-10x5L	28mm x 5M Bundle of 10 Speedpex Pipe						
28BPEX-10x6L	28mm x 6M Bundle of 10 Speedpex Pipe						

JGE 2095/DS JAN 05

All Dimensions in mm

THE COPYRIGHT IN THIS DRAWING AND THE PRODUCTS REFERRED THEREON BELONG TO JOHN GUEST INTERNATIONAL LIMITED AND THIS DRAWING NOR THE INFORMATION CONTAINED HEREIN SHALL BE PRODUCED IN ANY FORM OR USED FOR ANY PURPOSE WITHOUT WRITTEN CONSENT © 2007

The company has a policy of continuous research and development and reserves the right to amend without notice the specification and design of all products illustrated. For details of terms and conditions and any other technical enquiries, please contact our Customer Services Department.

ISSUE 8 GA 09-09-08

DS-BPEX
(sht 2 of 3 shts)

Product Data Sheet

Metric Five Layer Pex Barrier Pipe



John Guest

Product No.	Description (Nominal Diameter x Length)	Pipe O/D	Pipe I/D	Ovality
15BPEX -10x2L-DG	15mm x 2M Bundle of 10 Speedpex Pipe	14.9 - 15.1	11.45 - 11.65	1.0 Max
15BPEX -10x3L-DG	15mm x 3M Bundle of 10 Speedpex Pipe			
15BPEX -20X2L-DG	15mm x 2M Bundle of 20 Speedpex Pipe			
15BPEX -20X3L-DG	15mm x 3M Bundle of 20 Speedpex Pipe			
15BPEX -20X6L-B	15mm x 6M Bundle of 20 Speedpex Pipe			
15BPEX -20X6L-R	15mm x 6M Bundle of 20 Speedpex Pipe			
22BPEX-10x2L-DG	22mm x 2M Bundle of 10 Speedpex Pipe	21.9 - 22.1	17.6 - 17.8	1.0 Max
22BPEX -10x3L-DG	22mm x 3M Bundle of 10 Speedpex Pipe			
22BPEX -20X2L-DG	22mm x 2M Bundle of 20 Speedpex Pipe			
22BPEX -20X3L-DG	22mm x 3M Bundle of 20 Speedpex Pipe			
22BPEX -20X6L-B	22mm x 6M Bundle of 20 Speedpex Pipe			
22BPEX -20X6L-R	22mm x 6M Bundle of 20 Speedpex Pipe			

JGE 2095/DS JAN 05

All Dimensions in mm

THE COPYRIGHT IN THIS DRAWING AND THE PRODUCTS REFERRED THEREON BELONG TO JOHN GUEST INTERNATIONAL LIMITED AND THIS DRAWING NOR THE INFORMATION CONTAINED HEREIN SHALL BE PRODUCED IN ANY FORM OR USED FOR ANY PURPOSE WITHOUT WRITTEN CONSENT © 2007

The company has a policy of continuous research and development and reserves the right to amend without notice the specification and design of all products illustrated. For details of terms and conditions and any other technical enquiries, please contact our Customer Services Department.

ISSUE 8 GA 09-09-08

DS-BPEX

(sht 3 of 3 shts)