



Chemical protection

ULTRANEО 340

Splashes | continuous wear

Comfort with light chemical protection



CHEMICAL PROTECTION
TYPE A

EN388



2121X

EN ISO 374-1



TYPE A
CLMNST

EN ISO 374-5



EN407



X1XXXX

CATEGORY 3



0334

DEXTERITY

EN ISO 21420:
5/5

SPECIFIC ADVANTAGES



Comfort

- Suitable for long-term wear; added comfort of textile support
- Great dexterity, due to the gloves reduced thickness



Guaranteed quality

- Silicone free to prevent traces, defects on metal sheet and glass prior to painting



Care for the environment

- Recycled material in the packaging: 30 %

INDUSTRIES

- Automotive/mechanical industry
- Chemical industry
- Other industries

APPLICATIONS

- Handling and transporting chemicals
- Industrial cleaning, maintenance
- Timber treatment
- Battery, pump, and compressor manufacturing



Chemical protection

ULTRANEО 340

Splashes | continuous wear

LEGENDS

EN388	MECHANICAL HAZARDS
	PERFORMANCE LEVELS (X = NOT TESTED)
2 1 2 1 X	
0-4 0-5 0-4 0-4 A-F P	
	Impact protection (optional)
	Cut resistance according to ISO 13997
	Puncture resistance
	Tear resistance
	Blade cut resistance
	Abrasion resistance
EN407	THERMAL RISKS (HEAT AND FIRE)
	PERFORMANCE LEVELS (X = NOT TESTED)
X 1 X X X X	
0-4 0-4 0-4 0-4 0-4 0-4	
	Resistance to large quantities of molten metal
	Small splashes of molten metal
	Radiant heat resistant
	Convective heat resistance
	Contact heat resistance
	Limited flame spread
EN ISO 374-1	CHEMICAL RISKS
	C: Acetonitrile
	L: Sulphuric acid 96%
	M: Nitric acid 65%
	N: Acetic acid 99%
	S: Hydrofluoric acid 40%
	T: Formaldehyde 37%
TYPE A	
EN ISO 374-5	MICRO-ORGANISMS
	Protection against bacteria and fungi

PRODUCT DETAILS

Interior finish	Textile support
Exterior finish	Smooth
Material	Polychloroprene and natural latex
Cuff characteristic	Feston Cuff
Colour.s	Black
Length (cm)	38
Thickness (mm)	1.33
European sizes	7 8 9 10

LOGISTIC DETAILS

Packaging	1 pair/bag 5 pairs/box 50 pairs/carton
-----------	----------------------------------------------

LEGISLATION

- This product is not classified hazardous according to the regulation (EC) n°1272/2008 of the European Parliament and of the Council.
- This product does not contain more than 0.1 % of substance of very high concern (SVHC) or any substance included in the annex XVII of the regulation n° 1907/2006 of the European Parliament and of the Council (REACH).
- UE type certificate or CE type examination certificate: 0075/014/162/12/18/2964
- Issued by the notified body nr: 0075 CTC - 4, rue Hermann Frenkel - 69367 Lyon Cedex 07- FRANCE
- Quality assurance certificat: 0334 - Asqual 14 rue des Reculettes -75013 Paris - France