


# Product datasheet

Specifications



## FRONT PLATE TARIF INV+NSX630 W600 9M

LVS03272

EAN Code: 3606481872098

### Main

Range	PrismaSeT
Range of product	PrismaSeT G
Product or component type	Front plate
Accessory / separate part category	Installation accessory
Range compatibility	PrismaSeT PrismaSeT G enclosure
Type of front plate	Cut-out
Installed device	ComPact: fixed INV400 - control: direct front rotary handle - vertical installation ComPact: fixed NSX400 without earth leakage protection - control: toggle - vertical installation ComPact: fixed NSX400 with earth leakage protection - control: toggle - vertical installation ComPact: fixed INV400 - control: toggle - vertical installation
Poles description	1 x 4P: mounting plate support: INV400 vertical installation 1 x 4P: mounting plate support: NSX400 vertical installation
Operating position	Side by side

### Complementary

Enclosure/cubicle description	Floor-standing enclosure - width 600 mm Wall-mounted enclosure - width 600 mm
Number of vertical modules [50 mm]	9
Standards	IEC 61439-1 IEC 61439-2
Product certifications	ASTA
Surface finish	Textured Matt
Protective treatment	Electrophoresis treatment and hot-polymerised polyester epoxy powder
Colour	White (RAL 9003)
Height	450 mm
Width	600 mm
Net weight	1.58 kg
Quantity per set	Set of 1

<b>functional unit</b>	600 mm PrismaSeT G floor-standing enclosure ComPact INV400 fixed toggle vertical 4P 1 direct 600 mm PrismaSeT G wall-mounted enclosure ComPact INV400 fixed toggle vertical 4P 1 direct 600 mm PrismaSeT G floor-standing enclosure ComPact INV400 fixed direct front rotary handle vertical 4P 1 direct 600 mm PrismaSeT G wall-mounted enclosure ComPact INV400 fixed direct front rotary handle vertical 4P 1 direct 600 mm PrismaSeT G floor-standing enclosure ComPact NSX400 without fixed toggle vertical 4P 1 direct 600 mm PrismaSeT G wall-mounted enclosure ComPact NSX400 without fixed toggle vertical 4P 1 direct 600 mm PrismaSeT G floor-standing enclosure ComPact NSX400 with fixed toggle vertical 4P 1 direct 14 600 mm PrismaSeT G wall-mounted enclosure ComPact NSX400 with fixed toggle vertical 4P 1 direct 14
------------------------	--

## Environment

<b>IP degree of protection</b>	IP30
--------------------------------	------

## Packing Units

<b>Unit Type of Package 1</b>	PCE
<b>Number of Units in Package 1</b>	1
<b>Package 1 Height</b>	3 cm
<b>Package 1 Width</b>	46.5 cm
<b>Package 1 Length</b>	51.5 cm
<b>Package 1 Weight</b>	1.527 kg
<b>Unit Type of Package 2</b>	BB1
<b>Number of Units in Package 2</b>	6
<b>Package 2 Height</b>	11 cm
<b>Package 2 Width</b>	52.5 cm
<b>Package 2 Length</b>	52.5 cm
<b>Package 2 Weight</b>	9.937 kg
<b>Unit Type of Package 3</b>	P12
<b>Number of Units in Package 3</b>	24
<b>Package 3 Height</b>	35 cm
<b>Package 3 Width</b>	80 cm
<b>Package 3 Length</b>	120 cm
<b>Package 3 Weight</b>	51 kg

## Contractual warranty

<b>Warranty (in months)</b>	18
-----------------------------	----

## Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

### Environmental footprint

[Environmental Disclosure](#)

[Product Environmental Profile](#)

## Use Better

### Materials and Substances

Packaging made with recycled cardboard

Yes

Packaging without single use plastic

Yes

[EU RoHS Directive](#)

Compliant

REACH Regulation

[REACH Declaration](#)

Halogen-free status

Halogen free plastic parts product

PVC free

Yes

Silicone-free

Yes

## Use Longer

### Lifetime extension

Repair

No

## Use Again

### Repack and remanufacture

End of life manual availability

No need of specific recycling operations

Take-back

No