



1637

Air

Meet the lightest premium Protector™ case on the planet. Up to 40% lighter than other polymer cases.

Peli™ Air cases are the first in a series of remarkable innovations engineered by Peli, the pioneers of protective cases. For over 40 years Peli has designed and crafted the most influential protective cases in the world, and we're just getting started.

With the launch of the Peli™ Air line of cases, we're redefining the future of protection with a remarkable union of light and tough.

- Automatic pressure equalization valve - balances interior pressure, keeps water out
- Fold down over-molded handle
- Retractable extension trolley handle
- Stainless steel padlock protectors
- Business card holder
- Quiet rolling stainless-steel bearing wheels
- Press and Pull™ Latches
- Limited Lifetime Warranty
- Super-light proprietary HPX²™ Polymer - up to 40% lighter
- Waterproof O-ring seal
- User-customizable Pick N Pluck™ foam
- Waterproof, crushproof, dustproof
- IP67 & MIL-SPEC certified



CONFIGURATIONS



1637
Standard



1637NF
No Foam



1637WD
With Padded Dividers



1637WF
With Foam



WINE-12B
12-Bottle Wine

DIMENSIONS

Interior (L×W×D)	23.43 x 17.55" x 13.25 (59.5 x 44.6 x 33.7 cm)
Exterior (L×W×D)	26.61 x 20.65" x 14.87 (67.6 x 52.5 x 37.8 cm)
Lid Depth	2.00" (5.1 cm)
Bottom Depth	11.20" (28.4 cm)
Total Depth	13.2" (33.5 cm)
Int Volume	3.15 ft ³ (0.089 m ³)
Padlock Hole Diameter	0.31" (0.8 cm)

MATERIALS

Body	Proprietary Polypropylene Blend
Latch	ABS
O-Ring	EPDM
Purge Body	ABS
Purge Vent	Hi-Flow Gore-Tex 3 Micron Hydrophobic Non-Woven

COLOURS

 Black	 Orange	 Silver	 Yellow
---	--	--	--

WEIGHT

Weight With Foam	19.40 lbs (8.8 kg)
Weight Empty	15.20 lbs (6.9 kg)
Buoyancy	209.00 lbs (94.8 kg)

TEMPERATURE

Minimum Temperature	-60°F (-51.1 °C)
Maximum Temperature	160°F (71.1 °C)

OTHER

Wheels	2
---------------	---

ACCESSORIES

			
1506TSA TSA Lock	1500D Desiccant Silica Gel	1637AirDS Padded Divider Set	1637AirFS 7 pc. Replacement Foam Set

Peli
c/ Provença, 388, Planta 7 • Barcelona, Spain 08025 • Phone: +34 934 674 999
info@peli.com • www.peli.com

Document created on 05-09-25