



# Classic filament LED candles and lusters

## Classic LEDCandle ND 6.5-60W B35 E14 827 CL

Featuring a classic heritage design, Classic filament LED candles and lusters combine the familiar shapes of classic incandescent candle or luster with the benefits of the long lasting LED technology. They deliver beautiful, decorative warm-white light while saving around 90% on energy costs compared with traditional light candles and lusters.

### Product data

General Information	
Cap-Base	E14 [ E14]
EU RoHS compliant	Yes
Nominal Lifetime (Nom)	15000 h
Switching Cycle	20000X
Technical Type	6.5-60W
Light Technical	
Color Code	827 [ CCT of 2700K]
Luminous Flux (Nom)	806 lm
Color Designation	Warm White (WW)
Correlated Color Temperature (Nom)	2700 K
Luminous Efficacy (rated) (Nom)	124.00 lm/W
Color Consistency	<6
Color Rendering Index (Nom)	80
LLMF At End Of Nominal Lifetime (Nom)	70 %
Operating and Electrical	
Input Frequency	50 to 60 Hz
Power (Nom)	6.5 W

Lamp Current (Nom)	50 mA
Wattage Equivalent	60 W
Starting Time (Nom)	0.5 s
Warm Up Time to 60% Light (Nom)	0.5 s
Power Factor (Nom)	0.55
Voltage (Nom)	220-240 V
Temperature	
T-Case Maximum (Nom)	55 °C
Controls and Dimming	
Dimmable	No
Mechanical and Housing	
Bulb Finish	Clear
Approval and Application	
Energy Efficiency Label (EEL)	A++
Energy Consumption kWh/1000 h	7 kWh


# Classic filament LED candles and lusters

## Product Data

Full product code	871869964912800
Order product name	Classic LEDCandle ND 6.5-60W B35 E14 827 CL
EAN/UPC - Product	8718699649128
Order code	929002028002

Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	10
Material Nr. (12NC)	929002028002
Net Weight (Piece)	0.014 kg


## Dimensional drawing




Candle B35 60W 806lm 2700K E14 ND Clear

Product	D	C
Classic LEDCandle ND 6.5-60W B35 E14 827 CL	35 mm	97 mm


## Photometric data



LEDbulb 6,5-60W E14 B35




LEDbulb 6,5-60W E14 B35




LEDcandle E14 B35 827 CL

## Classic filament LED candles and lusters

### Lifetime



LEDbulb 6,5-60W E14 B35



LEDbulb 6,5-60W E14 B35

