

TRC750

High cut resistant fully coated latex glove

A fully dipped latex glove offering high cut and water protection, comfort and flexibility. Ideal to work in damp conditions.


Features

- ▲ Cut resistant: Level E / A5
- ▲ 13g liner with HPPE on the inside provides cut protection
- ▲ Fully encapsulated steel and nylon on the outside strengthens the protection against burrs and sharp edges
- ▲ Double dipped latex offers excellent water protection and high grip in the wet
- ▲ Contact heat protection up to 100°C for a short period (15 sec max)
- ▲ Seamless knit prevents irritation
- ▲ Elasticated wrist provides a secure fit
- ▲ RCS (Recycled Claim Standard) certified

29g
CO₂
savings



Certifications



Suitable industries & applications

Industries

- ▲ Construction
- ▲ Facilities Management
- ▲ Manufacturing

- ▲ Utilities
- ▲ Waste and Recycling

Applications

- ▲ Handling Sharp or Abrasive Materials
- ▲ Glass and Glazing

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment. The manufacturer reserves the right to make any modifications it deems necessary.

TRC750

High cut resistant fully coated latex glove

Product information

Materials	Liner:	13 Gauge Engineered HPPE, Nylon, Steel Fibre, HPPE
	Coating:	Foam Latex, Smooth Latex
Colour	Green / Black	
Length	240mm	
Cuff Style	Elasticated Knit Wrist	

Ordering information

S	SKG00080ED	Items per Pack 10 x Pairs
M	SKG00080EF	
L	SKG00080EH	Items per Case 120 x Pairs
XL	SKG00080EJ	
XXL	SKG00080EL	


Additional information

Certification legend



or click [here](#)

Declaration of conformity



or click [here](#)

View product online



or click [here](#)

Europe

sales@globus.com
+44 (0)161 877 4747
+44 (0)161 877 4746

Middle East & Africa

sales.gcc@globusgroup.com
+971 4 882 9962
+971 4 882 9963

Americas

salesusa@globusgroup.com
+1 83 337 54747

Globus Group, T2 Trafford Point, Twining Road, Trafford Park, Manchester, M17 1SH, UNITED KINGDOM
Globus EMEA FZE, Jafza One, Tower A, Office 2201, Jebel Ali, PO Box 61195, Dubai, UNITED ARAB EMIRATES
Globus Americas LLC, 45 Rockefeller Plaza, Suite 2000, New York City, New York, 10111, USA

The descriptions, characteristics, applications and photos are given for information purposes and do not constitute a contractual commitment.
The manufacturer reserves the right to make any modifications it deems necessary.