



Cut



Electrical

## Goatskin leather protectors, for extended high-voltage glove life and enhanced hand safety

- **Reinforced protection:** Composed of premium goatskin leather, ActivArmr® 96-003 protectors guard against moderate cut, puncture and abrasion risks, while ensuring additional personal protection for workers engaged in electrical work, either with or near energized components
- **Improved durability:** These leather protectors are specially designed to prolong electrical insulated gloves' wear life, deemed suitable for Class 1 to 4 gloves of this kind
- **Assured effectiveness:** Satisfying ASTM D120 and EN 60903 standards, ActivArmr® 96-003 leather protectors offer users proven, fully compliant hand protection
- **Heightened dexterity:** Their leather composition also enhances their dexterity, for unencumbered electrical PPE that remains easy to use



### Industries

- Electrical
- Industrial
- Automotive
- Automotive Aftermarket
- Manufacturing

### Applications

- Energized Electrical
- Electrical
- Maintenance

### Key Features

- **Robust goatskin leather:** Puncture, abrasion and cut resistance
- **Protective design:** For longer-lasting electrical safety gloves\*
- **Compliance to ASTM F696 and EN 388:** Proven capabilities \*suitable for wear over Class 1 to 4 electrical insulated gloves

### Performance Standards & Regulatory Compliance



### Specifications

| BRAND   STYLE    | DESCRIPTION                                                                                                                                                                           | Gauge | SIZE             | LENGTH | COATING COLOR  | PACKAGE      |
|------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|-------|------------------|--------|----------------|--------------|
| ActivArm® 96-003 | <b>Finishing:</b> Natural Leather Texture<br><b>Coating Material:</b> N/A<br><b>Liner Material:</b> Premium goatskin<br><b>Cuff Style:</b> Straight cuff with overedge binding fabric | N/A   | 8, 9, 10, 11, 12 | 12"    | Not Applicable | 1 piece/pack |

For additional information visit us at [www.ansell.com](http://www.ansell.com), or call us at

#### Europe, Middle East & Africa Region

Ansell Healthcare Europe NV  
Riverside Business Park  
Blvd International, 55  
1070 Brussels, Belgium  
T: +32 (0) 2 528 74 00  
F: +32 (0) 2 528 74 01

#### Latin America & Caribbean Region

Ansell Commercial Mexico S.A. de C.V.  
Blvd. Bernardo Quintana No. 7001-C,  
Q7001 Torre II,  
Suites 1304, 1305 y 1306,  
Col. Centro Sur, c.p. 76079  
Queretaro, Qro. Mexico  
T: +52 442 248 1544 / 248 3133

#### North America Region

Ansell Healthcare Products LLC  
111 Wood Avenue South,  
Suite 900  
Iselin, NJ 08830, USA  
T: +1 800 800 0444  
F: +1 800 800 0445

#### Canada

Ansell Canada  
105 Lauder  
Cowansville, QC J2K 2K8  
Canada  
T: +1 800 363 8340  
F: +1 800 267 3551

#### Australia

Ansell Limited  
Level 3, 678 Victoria Street,  
Richmond, Vic, 3121  
Australia  
T: +61 1800 337 041  
F: +61 1800 803 578

#### Asia Pacific Region

Ansell Global Trading Center  
(Malaysia) Sdn Bhd  
Prima 6, Prima Avenue  
Block 3512, Jalan Teknokrat 6  
T: +603 8310 6688  
F: +603 8310 6699